



UNITS IN INCHES

NOTES:

1. MEETS ALL CHANNEL REQUIREMENTS OF ISO/IEC 11801 AND ANSI/TIA-568-C.2
2. ENVIRONMENTAL: -40 TO +70C STORAGE, -10 TO +60C WITH RELATIVE HUMIDITY 95% NON-CONDENSING MAX. OPERATION
3. JACK ASSEMBLY: HOUSING FULLY SHIELDED ZINC ALLOY, NICKEL PLATE, INSERT CONTACTS PLATED 50 MICRO-INCHES OF GOLD, IDC ACCEPTS 22 TO 24 AWG WIRE.
4. MEETS UL & ULc 1863 SAFETY
5. RJ45 PLUG CYCLES = 750 MIN

<p>*** NOTICE ***</p> <p>THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED.</p> <p>NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND, INC.</p> <p>MANUFACTURING RELEASE. PRODUCT SPECIFICATIONS AND STANDARDS ARE SUBJECT TO CHANGE WITHOUT NOTICE.</p>			<p>legrand WWW.LEGRAND.US</p>		
<p>TITLE</p> <p>TOOLESS KEYSTONE JACK ASSEMBLY, SHIELDED, YY CATEGORY</p>			<p>REV 00</p>		
DWN	DP	11/2/2018	SIZE B	CAD FILE KSFTPYC	DWG NO KSFTPY
CHK	KC	11/2/2018	SCALE 2:1	SHEET 1 OF 1	
APPR	JF	12/20/2018			