

CABLE: 4 PAIR, 28 AWG, STRANDED, PVC, CMR

NOTE: XX = SPECIFY LENGTH IN FEET
YY = DENOTES COLOR


PART NO. (RDC610XX-YY)	COLOR
RDC610XX-00	BLACK
RDC610XX-02	RED
RDC610XX-04	YELLOW
RDC610XX-05	GREEN
RDC610XX-06	BLUE
RDC610XX-08	GRAY
RDC106XX-09	WHITE

ONLY STANDARD COLORS SHOWN.

LENGTHS AVAILABLE IN 1 FOOT INCREMENTS TO 25 FEET.

ELECTRICAL PERFORMANCE MEETS OR EXCEEDS ANSI/TIA-568-C.2 CAT 6A AND ISO/IEC 11801 CATEGORY 6A COMPONENT.

CONTACT TECHNICAL REPRESENTATIVE FOR APPLICATION USAGE.



8P8C PIN#	WIRE COLOR	8P8C PIN#	568B PAIRING
5	WHT/BLU	5	1
4	BLU	4	
1	WHT/ORG	1	2
2	ORG	2	
3	WHT/GRN	3	3
6	GRN	6	
7	WHT/BRN	7	4
8	BRN	8	

*** NOTICE ***
THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF LEGRAND, INC.



WWW.LEGRAND.US

TITLE

CORD, REDUCED DIAMETER-6A UTP, MOD 8, XX FT, YY COLOR, 4P, 28AWG, ST, PVC, CMR

	NAME	DATE	SIZE	CAD FILE	DWG NO	REV
DWN	KC	4/20/2016	A	RDC610XXYYC	RDC610XX-YY	01
CHK	CAC	4/19/2016	SCALE 1:2		WEIGHT	SHEET 1 OF 1
APPR	GJL	4/20/2016				