


SPECIFICATION SHEET



Basic Power Distribution Unit

Basic PDUs are a reliable single-phase system to distribute power with a single input to multiple outputs

OVERVIEW

Single-phase basic PDUs deliver stalwart reliability and simple installation. Standardized power distribution enables cost-effective scaling, speed to deployment, and simplifies procurement due to a common platform.

FEATURES

- Integrated Locking Outlets on IEC Receptacles: Eliminates the need for special power cords that lock at the PDU
- Rotatable Cord: Enables maximum flexibility for routing the input plug—simplifying the installation of Zero U PDUs
- Mounting Types: Available in horizontal and vertical configurations to ensure power distribution is optimally located
- Hydraulic-Magnetic Breakers: Provide less heat dependent local protection and quick recovery from circuit overload by utilizing a two-step response curve—these breakers provide a delay on normal overcurrents, while tripping quickly on short circuits

ITEM DESCRIPTION

LP-21310 Rack PDU, Basic, 1U, 24A, 120V, (10) 5-20R, L5-30P Cord

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

- RoHS: Yes
- UL Listed: Yes
- FCC: Yes



designed to be better.™



SPECIFICATION SHEET

SPECIFICATIONS:

Basic Power Distribution Unit LP-21310 - Rack PDU, Basic, 1U, 24A, 120V, (10) 5-20R, L5-30P Cord

SPECIFICATIONS

INPUT

- Input Plug: NEMA L5-30P (2P3W)
- Cord Length: 3 meters (9.84 feet) standard
- Cord Entry: Bottom-front feed
- Cable Type: IP44("splashproof")
- Number of Power Cords: 1
- Maximum Input Current: 30A
- Nominal Input Voltage: 120V, Single phase
- Rated Input Voltage: 100-120V
- Input Frequency: 50/60Hz
- Power Capacity: 2.4kVA at 100V, 2.9kVA at 120V

OUTPUT

- Nominal Output Voltage: 120V
- Rated Output Voltage: 100-120V
- Receptacles (Output Connections): (10) NEMA 5-20R, 12A
- Securelock Support: No
- Cord Retention: No
- Overload Protection: (2)1-pole, 16A, Airpax breaker

PHYSICAL


- Color: Black & Silver
- Unit Dimensions (WxDxH): 436mm x 133mm x 44mm; 17.2" x 5.2" x 1.7"
- Form Factor: 1U
- Mounting: 1U Horizontal Mounting L-Bracket

ENVIRONMENTAL

- Operating Temperature: 45°C
- Operating Relative Humidity: 85%
- Operating Elevation: 0-10000ft

CONFORMANCE

- Regulatory Approvals: UL Listed, Canada ICES-003, Part 15 Class A of the FCC rules, RoHS compliant
- Warranty: Standard 2 years manufacturer warranty



MOUNTING BRACKET (2) INCLUDED



Legrand, North and Central America

60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us