

LBV-xx-x	RU	"A"	"B"	"C"	"D"
LBV-20-x	20	35.125	16	20	17.562
LBV-24-x	24	42.125	20	24	21.062
LBV-25-x	25	43.875	20	24	21.937
LBV-30-x	30	52.625	28	28	26.312
LBV-35-x	35	61.375	32	32	30.687
LBV-40-x	40	70.125	36	40	35.062
LBV-42-x	42	73.625	40	40	36.812
LBV-45-x	45	78.875	40	44	39.437
LBV-47-x	47	82.375	44	44	41.875
LBV-48-x	48	84.125	44	48	42.062
LBV-50-x	50	87.625	48	48	43.812

DWG. NO.
S-LBV-xx-x

NOTE:

INCLUDES:

- (3) 1/4-20 X 3/4 SEPARATED WASHER HEAD BOLT
- (3) 1/4-20 UNISTRUT NUTS
- (10) 1/2 x 8 HOOK + LOOP (VELCRO) CABLE TIE

