Concerto.

NuVo's Grand Concerto invites true audio excellence into your home, for a rich listening experience of high quality sound and nearinfinite variety.



With the Concerto, it's about your music, sounding full, crisp and clear, wherever you want it. With its staggering power and the luxury of sharing the pristine listening experience with up to eight zones simultaneously, the Grand Concerto leaves no corner of your home untouched.

But the delight doesn't stop with power and performance; the Grand Concerto also delivers incredible variety, supporting up to six audio devices at once. Whether you dock your iPod, or pull from your favorite customized online radio station*, the music you love most is right at your fingertips.

Plus with several sleek and simple control options to pick from, your guaranteed a custom whole home audio solution that's elegant, easy, and perfect for you.

*Internet Radio requires use of Music Port (MPS4 or MPS4-E)



- The most powerfully amplified system for large room and open space zones
- Direct wiring for clean audio transfer without distortion or interruption
- Music can be shared in eight rooms, all playing the same song or different tunes at once
- A variety of six different inputs allows each person to customize and listen to whatever they want
- High-performance amplifier operates coolly and saves energy
- Displays Song and Album information from an NuVoNet Smart Audio Source Component for easy navigation
- Using RS-232, music can be accessed and controlled through a whole home automation system
- A Concerto[®] Expander can add up to eight additional rooms of music to accommodate all areas of the home, even the garage, for a full system of sixteen zones



Concerto (NV-I8GM).

Specifications

Zones 1-6 Power Amplifier Outputs		Zone Trigger Outputs	
Continuous Average Output Power	80W (40W x 2)	Output Power	12VDC @ 50mA
Two channels driven 30-20khz @ 1% THD		Outputs	8 (zones 1-8)
Rated Distortion (1/2 Power)	0.40%		
Rated Impedance	6 ohm	Source Status	
Damping Fator	50+	Output Power	3-15 VDC
Frequency Response	20-20kHz	Outputs	6 (sources 1-6)
Zones 1-8 Preamplifier Outputs		Power Requirements	
Variable Output	0-600mV RMS	Power Supply	
Fixed Output	600mV RMS	18GMS	110V 50/60Hz
Impedance	600 ohm	I8GMS-EX	240V 50/60Hz
		Power Consumption all channels	
Source Inputs 1-6		driven to full-rated power	600VA (480W)
Input Impedance	20K	Power Consumption average	
Input Sensitivity for Rated Power	300mV RMS	operating conditions	100VA (80W)
Input Overload	3V RMS	Power Consumption no signal	30VA (25W)
Emitter Outputs		Regulatory Approvals	
Source Outputs	6	I8GMS: ETL	
Sum Outputs	2	I8GMS-EX: CE, C-Tick, ETL	
Output Drive Current	100mA		
Output Drive Voltage	12VDC	Physical Specifications	
Compatible with single and dual emitters		Unit Size (mm)	95 H x 430 W x 340 D
		Unit Size (inch)	3 3/4 H x 17 W x 13 3/8 D
System		Unit Weight (kg)	9.4
System On (output)	12VDC @ 50mA	Unit Weight (lbs)	20.6
External Mute	3-12VDC	-	
		Shipping Specifications	

380 H x 600 W x 475 D 15 H x 23 5/8 W x 18 3/8 D 15.5 34

NuVo reserves the right to change specifications without notice.

Shipping Size (mm)

Shipping Size (inch)

Shipping Weight (kg)

Shipping Weight (lbs)