

Nuvo® P200 Player

Allowing for both wired and wireless setup, the P200 player provides the ultimate installation flexibility while delivering 120 watts of high-fidelity audio from a near-infinite selection of streaming music to a single zone. Ideal for reaching hard-to-wire rooms and easily expanding Player Portfolio systems, this player blends performance and flexibility like never before.



- High-fidelity audio is delivered to every area of your home, and kept perfectly in sync.
- Compatible with Legrand's other Nuvo Player Portfolio products for a truly custom, easily expandable system (up to sixteen zones).
- Supports both wired ethernet and wireless 802.11n configuration options adding flexibility for any home.
- Includes 802.11n wireless capability and utilizes both 2.4 and 5 Ghz bands, for fast signals and broad coverage.
- All your favorite music is right at your fingertips with easy access to networked computers, streaming Internet Radio, and even audio content stored on any Android or iOS device.
- Connect to storage devices, analog equipment, or home theater receivers through the unit's audio line-in, line-out, or USB ports.
- Connect any Bluetooth device wirelessly, streaming audio from apps and services on your personal device throughout your system.
- Manage your music via the convenient wall-mounted P10 keypad or wirelessly from the palm of your hand with free apps for your Apple or Android device.

Streaming services subject to geographic availability.

Nuvo® P200 Player

Input/Output Connectors

Line Input	1 - TRS 3.5 mm stereo jack
Line Output	1 - TRS 3.5 mm stereo jack
Speaker Output 4 - Gold 5-way binding post	
USB 2.0 Connection (Type A)	1
Local Area Network (LAN)	1 - RJ45

Supported Audio Formats

Music File (via USB or network)	MP3
	WMA
	AAC
	Ogg Vorbis
	FLAC
	WAV

Internet Radio:	Pandora
	Sirius/XM
	iHeart Radio
	Spotify
	Tuneln
	Deezer
	Napster

IP Control	Apple iPod®
	Apple iPhone®
	Apple iPad®
	Android Mobile
	Android Tablet

Network Connectivity

LAN (Wired Connection)	10/100base-t Ethernet
Wireless Connection	MIMO, 2 TX + 2 RX Channels
	IEEE 802.11a/b/g/n
	Wi-Fi Alliance CERTIFIED™

Amplifier Output

Rated Output Power (8 ohm)	120W (60W x 2)
Two channels driven 20 Hz	20 KHz @ 0.5% distortion
Rated Output Power (4 ohm)	120W (60W x 2)
Two channels driven 20 Hz	20 KHz @ 0.5% distortion
Rated Distortion (1/2 Power)	0.20%
Speaker Impedance	4 – 8 ohms
Frequency Response (20 - 20kHz)	+/-0.5 dB
Damping Factor	65+
Signal-to-Noise Ratio at rated output	92 dB A – weighted

SPECIFICATIONS

Line Output:

Output Level	0-1000 mV RMS
Output Impedance	5 Ohms
Signal-to-Noise Ratio at rated output	88 dB A – weighted

Line Input:

Input Impedance	10 KOhms
Input Overload	2.3 V RMS

Audio Processing

Bass Equalization	+/-12 dB range
Treble Equalization	+/-12 dB range
Balance	

Regulatory Approvals

Safety	cTUVus, CE-LVD
EMC	FCC, IC, CE-EMC, C-Tick
Environmental Compliance	RoHS

Power Requirements

Input Voltage	100 – 240VAC, 50/60 Hz
Power Consumption (max)	150 W
Power Consumption (typical – 1/8 audio power)	31 W

Operating Temperature

0° C to 40° C

Physical Specifications

Unit Size (mm)	43 H x 247 W x 175 D
Unit Size (inch)	1.69 H x 9.72 W x 6.89 D
Unit Weight (kg)	1.20
Unit Weight (pounds)	2.65

Shipping Specifications

Unit Size (mm)	360 L x 240 W x 66 H
Unit Size (inch)	14.17 L x 9.45 W x 2.60 H
Unit Weight (kg)	2.00
Unit Weight (pounds)	4.41

Languages Supported

English, Spanish, French
Portuguese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™



Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nvuo