

AccentPLUS1 6.5" Outdoor Speaker.

Specifications

Speaker Components

Tweeter Magnet: Neodymium
Dome: PEI (Polyetherimide), 3/4" (19mm)
Type: Fixed Position

Woofers Magnet Structure: Ferrite
13oz (370g) Flat Black Plate
Voice Coil: 1" (25mm) Polyimide Film
Cone: 6.5" (165mm) Polypropylene
Surround: Butyl Rubber
Dust Cover: Polypropylene

Cabinet Material Mineral Filled Polyethylene
Grill Material Powder Coated Aluminum
Bracket Material Powder Coated Steel

Crossover

Tweeter 12dB
Woofers N/A

Electrical

Power Rating 50W
Impedance 8 ohm
Frequency Response 60Hz-20kHz +/- 3dB
Efficiency 88 dB 1W/1M

Mechanical

Dimensions (HxWxD) 13" x 7 5/8" x 7 1/2"
330mm x 193mm x 190mm
Depth w/ bracket 8"
205mm
Speaker Weight 7.50 lbs
3.4 kg

NuVo reserves the right to change specifications without notice.