

# NV-T2DAB Tuner.

## Specifications

### Power Requirements

AC Power Input	90-264 VAC 50/60Hz
Power Consumption, standby	1 W max.
Memory Backup	Indefinite

### DAB

Tuning Range (Band III)	174.928 to 239.200 MHz
Antenna/Aerial Input	75 $\Omega$ (unbalanced)

### FM

Tuning Range	87.5 to 108.0 MHz
De-emphasis	50/75 $\mu$ s
Antenna/Aerial Input	75 $\Omega$ (unbalanced)

### Audio Output

Level	Two Stereo Outputs
Impedance	1 Vrms
	470 ohm

### Infrared Input

Input Voltage	3-15 V
Input Carrier Frequency	38 kHz nominal
Polarity	Active High

### Regulatory Approvals

Intertek Listed (cETLus)
USA Safety Listing (UL 60065)
FCC
CE
Australia C-Tick
Canada Safety Listing (CAN/CSA-C22.2 60065:03)

### Physical Specifications

Unit Size (mm)	44 H x 430 W x 250 D
Unit Size (inch)	1.75 H x 17 W x 9.875 D
Shipping Size (mm)	205 H x 515 W x 343 D
Shipping Size (inch)	8 H x 20 W x 13.5 D
Unit Weight (kg)	2.36
Unit Weight (lbs)	5.20
Shipping Weight (kg)	6.5
Shipping Weight (lbs)	14.3

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904

Office Direct: 859.817.7200

Email: [sales@nuvotechnologies.com](mailto:sales@nuvotechnologies.com)

Web: [www.nuvotechnologies.com](http://www.nuvotechnologies.com)