

Nuvo® P3500 Professional Series Player

At a powerful 100 watts per zone, the Nuvo P3500 Professional Series Player uniquely delivers high-fidelity audio to three independent zones from a single, rack-mount unit, offering unprecedented performance and flexibility. Whether upgrading an existing system, or starting a new installation, the P3500 features built-in streaming source variety, the cleanest audio reproduction, and simple integration with third party automation solutions, all to perfectly fit into any home.



- Unprecedented musician-grade, high-fidelity audio is delivered to three separate areas of your home from a single, rack-mountable unit.
- Compatible with Legrand's other Nuvo players for a truly custom, flexible installation solution.
- Hard-wire multiple players with Ethernet for a clean, centralized installation easily expandable (up to sixteen zones).
- All your favorite music is right at your fingertips with easy access to networked computers, streaming Internet Radio, and even audio content stored on any Android or iOS device.
- Connect to storage devices, analog equipment, or home theater receivers through the unit's audio line-in, line-out, or USB ports.
- Manage your music via the convenient wall-mounted P10 keypad, P30 Touch Screen, or wirelessly from the palm of your hand with free apps for your Apple or Android device.
- Exceptional sound quality is matched with extreme power efficiency for superior amplification.

Streaming services subject to geographic availability.

Nuvo® P3500 Professional Series Player

Input/Output Connectors

Line Input	3 - Dual RCA
Line Output	3 - Dual RCA
Trigger Input	3 - TS 3.5 mm stereo jack
Trigger Output	3 - TS 3.5 mm stereo jack
Speaker Output	3 - (4 contact) pluggable
USB 2.0 Connection (Type A)	3 (Zone 3 on Front)
Local Area Network (LAN)	1 - Dual RJ45

Supported Audio Formats

Music File (USB or over network)	MP3
	WMA
	AAC
	Ogg Vorbis
	FLAC
	WAV

Internet Radio:	Pandora
	Napster
	SiriusXM
	iHeart Radio
	TuneIn
	Spotify
	Deezer

IP Control

Apple iPod®
Apple iPhone®
Apple iPad®
Android Mobile
Android Tablet

Network Connectivity

LAN (Wired Connection)	10/100base-t Ethernet
	Internal Ethernet switch to 3 independent zone nodes

Amplifier Output (typical of 3 zones)

Rated Output Power (1KHz / 1% Distortion)	4 Ohm - 200W (100W x 2)
	6 Ohm - 150W (75W x 2)
	8 Ohm - 100W (50W x 2)
Total Harmonic Distortion (1/2 Power)	100Hz - 0.003%
	1KHz - 0.003%
	6.67KHz - 0.020%
Speaker Impedance	4 / 6 / 8 ohms
Frequency Response (20 - 20kHz)	+/-0.5 dB
Damping Factor	80+
Signal-to-Noise Ratio (IHF-A)	100 dB

SPECIFICATIONS

Line Output:

Output Level	0-2.1V RMS
Output Impedance	470 Ohms
Signal-to-Noise Ratio (IHF-A)	100 dB

Line Input:

Input Impedance	100K Ohms
Input Overload	2.3 V RMS

Audio Processing

Bass Equalization	+/-12 dB range
Treble Equalization	+/-12 dB range
Balance	
Loudness compensation	

Regulatory Approvals

Safety	cTUVus, CE-LVD
EMC	FCC, IC, CE-EMC, C-Tick
Environmental Compliance	RoHS

Power Requirements

Input Voltage	100 – 240VAC, 50/60 Hz
Power Consumption (max)	680 W
(typical - music)	260 W
(UL60065 - 1/8 power)	120W

Operating Temperature

0° C to 40° C

Physical Specifications

Unit Size without feet (mm)	44 H x 430 W x 250 D
Unit Size without feet (inch)	1.73 H x 16.93 W x 9.84 D
Unit Size with feet (mm)	54 H x 430 W x 250 D
Unit Size with feet (inch)	2.13 H x 16.93 W x 9.84 D
Unit Weight (kg)	3.50
Unit Weight (pounds)	7.70

Shipping Specifications

Unit Size (mm)	565 L x 328 W x 130 H
Unit Size (inch)	22.24 L x 12.91 W x 5.12 H
Unit Weight (kg)	4.90
Unit Weight (pounds)	10.80

Languages Supported

English, Spanish, French
Portuguese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™



Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nvuo