

Nuvo® P400 Player Portfolio Tabletop Speaker

Putting the music you love in any room of the home. The Player Portfolio Tabletop Speaker (NV-P400-XX) provides superior sound quality through a powerful 2.1 system. The sleek P400 brings pure, clean sound to any room of the home and is used as a single zone for the Nuvo Player Portfolio System allowing access to networked audio content and a variety of streaming services.



- Superior sound quality with powerful 2.1 system, complete with a five and a quarter inch subwoofer, two midrange drivers and two tweeters
- Simple control with the top-mounted LED controls, Nuvo in-wall Keypads, and the Nuvo Player app for iOS and Android devices
- Use as a Player zone giving you access to networked content or streaming services such as Spotify, Pandora, iHeartRadio, and more
- Sleek design with metal grill and capacitive touch backlit control
- 3.5mm analog audio and USB 2.0 inputs
- Third-party integration with control partners such as Crestron, Control4, KNX, RTI, URC, and more
- Ethernet or Wireless 802.11 a,b,g,n, 2.4GHz or 5GHz

*Streaming services subject to geographic availability. Service subscriptions may be required.

Nuvo® P400 Player Portfolio

Tabletop Speaker

Input/Output Connectors

Line Input	3.5mm combination analog
USB Connection	Two
Local Area Network (LAN)	RJ45, Cat5 minimum, 10/100baseT minimum

Supported Audio Formats

Music File (USB or over network):	MP3 WMA AAC Ogg Vorbis FLAC WAV
-----------------------------------	------------------------------------------------

Internet Radio:	Pandora Sirius/XM Napster iHeart Radio Spotify Connect TuneIn Deezer
-----------------	----------------------------------------------------------------------------------------

Third Party Compatability:	URC RTI Crestron Control4 Bit Wise Vantage KNX
----------------------------	------------------------------------------------------------------

IP Control:	Apple iTouch® Apple iPhone® Apple iPad® Android Mobile Android Tablet
-------------	-----------------------------------------------------------------------------------

Network Connectivity

LAN (Wired Connection)	Ethernet,
	Wireless: 802.11 a,b,g,n 2.4 GHz or 5GHz band

Output

Frequency Response	50Hz - 20KHz
--------------------	--------------

Line Input:

Input Impedance	10 Kohms
-----------------	----------

SPECIFICATIONS

Input Overload	2.2 V RMS
----------------	-----------

Regulatory Approvals

Safety	cTUVus, CE-LVD
EMC	US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003; EUROPE:CISPR13; EUROPE: 55020; AUSTRALIA/NEW ZEALAND: C-TICK standard AS/NZS CISPR13

Environmental Compliance	RoHS
--------------------------	------

Power Requirements

Input Voltage	110 – 240VAC, 50/60 Hz
Power Consumption (max)	80 W
(typical - music)	50 W

Operating Temperature

0° C to 40° C

Physical Specifications

Material:	Metal/Plastic
Color:	Black

Unit Size without feet (mm)	217 H x 368 W x 149 D
Unit Size without feet (inch)	8.56 H x 14.5 W x 5.88 D

Unit Size with feet (mm)	217 H x 368 W x 149 D
Unit Size with feet (inch)	8.56 H x 14.5 W x 5.88 D

Unit Weight (kg)	4.69
Unit Weight (pounds)	10.35

Shipping Specifications

Unit Size (mm)	483 L x 228 W x 287 H
Unit Size (inch)	19 L x 8.9 W x 11.3 H

Languages Supported

English, Spanish, French
Portuguese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™



Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo