

Nuvo® P4300 Professional Series Player

Providing 110 watts of power per zone, this single rack-mount Professional Series Player (NV-P4300-XX) delivers high fidelity audio to three independent zones. Your music is always in hand with built-in access to streaming services and the ability to play content from networked computers and your iOS and Android devices. With a backlit touchscreen for configuration, system status, and the ability to show zone names, the P4300 Player is the latest generation of the Nuvo Professional Series Players.



- Built-in access to streaming services - Spotify, iHeartRadio, TuneIn, Napster, Deezer and SiriusXM
- Easily play music from networked computers, as well as iOS and Android devices.
- Backlit touchscreen supports easy setup with visible system status, zone names, and more
- A single rack-mount unit delivers high fidelity audio to three independent zones
- Efficient Class D amplifiers with 110 watts per zone at 8, 6 or 4 ohms
- Side mounted heat sinks and no fans for convenient single-space rack mounting
- 3.5mm combination analog/TOSLINK jacks for line inputs and outputs

*Streaming services subject to geographic availability. Service subscriptions may be required.

Nuvo® P4300

Professional Series

Player

Input/Output Connectors

| | |
|--------------------------|--------------------------------------------|
| Line Input | 3.5mm combination analog / TOSLINK |
| Line Output | 3.5mm combination analog / TOSLINK |
| Trigger Output | 12 volt 3.5 mm |
| Speaker Output | 14 ga. four position phoenix connectors |
| USB Connection | Three, One per zone |
| Local Area Network (LAN) | RJ45, Cat5 minimum, 10/100baseT minimum |

Supported Audio Formats

| | |
|----------------------------------|------------|
| Music File (USB or over network) | MP3 |
| | WMA |
| | AAC |
| | Ogg Vorbis |
| | FLAC |
| | WAV |

| | |
|-----------------|--------------|
| Internet Radio: | Pandora |
| | Sirius/XM |
| | iHeart Radio |
| | Napster |
| | Deezer |
| | Tuneln |
| | Spotify |

| | |
|------------|----------------|
| IP Control | Apple iTouch® |
| | Apple iPhone® |
| | Apple iPad® |
| | Android Mobile |
| | Android Tablet |

Network Connectivity

| | |
|------------------------|------------------------------------------------------|
| LAN (Wired Connection) | 10/100base-t Ethernet |
| | Internal Ethernet switch to 3 independent zone nodes |

Amplifier Output (typical of 3 zones)

| | |
|-------------------------------------------|--------------------------------|
| Rated Output Power (1KHz / 1% Distortion) | 4 / 6 / 8 Ohms - 110W per zone |
|-------------------------------------------|--------------------------------|

| | |
|---------------------------------|-----------------------------------|
| Distortion | .01 THD+N |
| Speaker Impedance | 4 / 6 / 8 Ohms |
| Frequency Response (20 - 20kHz) | +/-1 dB |
| Signal-to-Noise Ratio (IHF-A) | 104 dB on speaker output @ 4 Ohms |

SPECIFICATIONS

Line Output:

| | |
|------------------|----------|
| Output Level | 2 V RMS |
| Output Impedance | 470 Ohms |

Line Input:

| | |
|-----------------|----------|
| Input Impedance | 20K Ohms |
| Input Overload | 2 V RMS |

Regulatory Approvals

| | |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Safety | cTUVus, CE-LVD |
| EMC | US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003; EUROPE:CISPR13; EUROPE: 55020; AUSTRALIA/NEW ZEALAND: C-TICK standard AS/NZS CISPR13 |
| Environmental Compliance | RoHS |

Power Requirements

| | |
|-------------------------|------------------------|
| Input Voltage | 110 – 240VAC, 50/60 Hz |
| Power Consumption (max) | 260 W |
| (typical - music) | 50 W |

Operating Temperature

0° C to 40° C

Physical Specifications

| | |
|-------------------------------|----------------------------|
| Unit Size without feet (mm) | 47 H x 430 W x 258 D |
| Unit Size without feet (inch) | 1.85 H x 16.93 W x 10.16 D |
| Unit Size with feet (mm) | 54 H x 430 W x 258 D |
| Unit Size with feet (inch) | 2.13 H x 16.93 W x 10.16 D |
| Unit Weight (kg) | 2.9 |
| Unit Weight (pounds) | 6.45 |

Shipping Specifications

| | |
|----------------------|----------------------------|
| Unit Size (mm) | 565 L x 330 W x 130 H |
| Unit Size (inch) | 22.24 L x 12.99 W x 5.12 H |
| Unit Weight (kg) | 3.92 |
| Unit Weight (pounds) | 8.65 |

Languages Supported

English, Spanish, French
Portuguese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™



Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo