Nuvo®

Delivering a stand-out bass response, the 10" Powered Subwoofer brings a whole new dimension of deep and detailed clarity to movies and music. With a front-mounted woofer, dual ports and an efficient all-digital 200 watt amplifier, the NV-SUB10 adds a powerful low-frequency impact to mid-sized home theater or audio installations. Its cabinet is constructed of durable MDF for a distortion-free, superior bass experience.

- Powerful front-mounted 10" subwoofer ideal for mid-sized audio installations
- Installation-friendly front-firing woofer and dual ports
- Efficient all-digital 200 watt amplifier
- Durable MDF enclosure construction ensures distortion-free bass response
- Unfiltered LFE (low frequency effects) input, RCA stereo input and output, and USB port
- Signal-sensing power ON/OFF
- Variable crossover and phase adjustment
- Woofer has lifetime warranty and amplifier has two year warranty

The NV-SUB10 features signal-sensing power activation (optional setting) to automatically turn on the subwoofer when it receives a signal from the receiver. It will return to standby after 15 minutes of no signal.

Offering maximum versatility, the Powered Subwoofers were designed to integrate with almost any audio system. Unfiltered LFE / RCA stereo input and output let you easily connect to most modern receivers. And a convenient USB jack can power an optional wireless receiver. The variable crossover and phase controls allow you to match the Subwoofer output with the main speakers for premium performance and sound.





Nuvo® NV-SUB10 Subwoofer

Materials

Vinyl covered MDF cabinet

Output

Speaker Impedance 8 Ohms
Power Consumption 30 watts typical 240 watts max
Output Power 200 watts

Frequency 27Hz - 200Hz
Line Output Connector RCA analog (pair)

Operating Temperature 5° - 35° C 41° - 95° F

Input

Line Input Connector LFE / RCA analog (pair)
Input Voltage 110v - 220v (manual switch)
Line Input Overload 8 volts

Regulatory Approvals

cTUVus, CE-LVD US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003 EUROPE:CISPR32; EUROPE: EN 55032:2012; AUSTRALIA/NEW ZEALAND: RCM Standard AS/NZS CISPR32 ROHS (Restriction of Hazardous Substances Directive 2002/95/EC

Weight

Unit Weight (kg) 13 kg
Unit Weight (lbs) 28.6 lbs
Shipping Weight (kg) 15.8 kg
Shipping Weight (lbs) 34.8 lbs

Unit Size

Unit Size (mm) 388.6 L x 373.4 W x 406.4 H
Unit Size (inch) 15.3 L x 14.7 W x 16 H

Unit Size without feet

Unit Size (mm) 373.4 L x 373.4 W x 406.4 H
Unit Size (inch) 14.7 L x 14.7 W x 16 H

Shipping Specifications

Unit Size (mm) 508 L x 508 W x 525.8 H
Unit Size (inch) 20 L x 20 W x 20.7 H

Legrand reserves the right to change specifications without notice.





designed to be better™



Legrand, North America

3015 Kustom Drive Hebron, KY 41048 United States 844.334.8044 www.legrand.us/nuvo