

NUVO SPEAKERS

3 UNIQUE SERIES TO FIT ANY SPACE PROJECT, AND PRICE POINT
 BEAUTIFUL, BEZELESS MAGNETIC GRILLS
 PIVOTING TWEETERS
 3 DOG LEG DESIGN FOR FASTER INSTALLATION ON IN-CEILING MODELS

SERIES TWO

Impedance
8 Ohms
Sensitivity
86dB
Power
50w RMS / 100w Peak
Woofer Material
Poly
Tweeter Material
Silk

							
Overall Dimensions	9.06" / 230mm	9.06" / 230mm	9.06" / 230mm	10.63" / 270mm	11.22" / 285mm	8.66" x 11.81" / 220mm x 300mm	15.35" x 7.48" / 390mm x 190mm
Cutout Dimensions	8.07" / 205mm	8.07" / 205mm	8.07" / 205mm	9.68" / 246mm	10.15" / 258mm	7.6" x 10.79" / 194mm x 274mm	6.41" x 14.3" / 163mm x 363mm
Woofer Size	6.5"	6.5"	6.5"	8"	8"	6.5"	5.25"
Tweeter Size	0.5"	0.5"	0.5"	0.5"	0.5"	0.5"	0.5"
Mounting Depth	3.9" / 99mm	4.57" / 116mm	3.9" / 99mm	4.37" / 111mm	5.31" / 135mm	3.27" / 83mm	3.35" / 85mm
Frequency Response	60Hz - 20KHz	60Hz - 20KHz	55Hz - 20KHz	45Hz - 20KHz	45Hz - 20KHz	60Hz - 20KHz	65Hz - 20KHz
Shipping	Pair	Single	Single	Pair	Single	Pair	Single






SERIES FOUR

Impedance
8 Ohms
Sensitivity
88dB
Power
75w RMS / 150w Peak
Woofer Material
Glass Fiber
Tweeter Material
Aluminum

							
Overall Dimensions	9.06" / 230mm	9.06" / 230mm	9.06" / 230mm	10.63" / 270mm	11.22" / 285mm	8.66" x 11.81" / 220mm x 300mm	15.35" x 7.48" / 390mm x 190mm
Cutout Dimensions	8.07" / 205mm	8.07" / 205mm	8.07" / 205mm	9.68" / 246mm	10.15" / 258mm	7.6" x 10.79" / 194mm x 274mm	6.41" x 14.3" / 163mm x 363mm
Woofer Size	6.5"	6.5"	6.5"	8"	8"	6.5"	5.25"
Tweeter Size	0.75"	0.75"	0.75"	0.75"	0.75"	0.75"	0.5"
Mounting Depth	3.94" / 100mm	4.76" / 121mm	3.94" / 100mm	4.41" / 112mm	5.55" / 141mm	3.27" / 83mm	3.35" / 85mm
Frequency Response	55Hz - 20KHz	55Hz - 20KHz	50Hz - 20KHz	40Hz - 20KHz	40Hz - 20KHz	55Hz - 20KHz	60Hz - 20KHz
Shipping	Pair	Single	Single	Pair	Single	Pair	Single

SERIES SIX

Impedance
8 Ohms
Sensitivity
89dB
Power
100w RMS / 200w Peak
Woofer Material
Kevlar® / Carbon Fiber Weave
Tweeter Material
Titanium

						
Overall Dimensions	9.06" / 230mm	9.06" / 230mm	10.63" / 270mm	11.22" / 285mm	8.66" x 11.81" / 220mm x 300mm	8.66" x 17.71" / 220mm / 450mm
Cutout Dimensions	8.07" / 205mm	8.07" / 205mm	9.68" / 246mm	10.15" / 258mm	7.6" x 10.79" / 194mm x 274mm	7.6" x 16.65" / 193mm x 423mm
Woofer Size	6.5"	6.5"	8"	8"	6.5"	6.5"
Tweeter Size	1"	1"	1"	1"	1"	1"
Mounting Depth	3.94" / 100mm	4.76" / 121mm	4.41" / 112mm	5.55" / 141mm	3.27" / 83mm	3.5" / 90mm
Frequency Response	60Hz - 20KHz	60Hz - 20KHz	35Hz - 20KHz	35Hz - 20KHz	50Hz - 20KHz	45Hz - 20KHz
Shipping	Pair	Single	Pair	Single	Pair	Single

All speakers come with beautiful, bezeless magnetic speaker grills; easily paintable with removable scrim cloths.



Custom mounting brackets provide accurate and efficient installs.

