



Fill your home with high fidelity music.

Nuvo[®]



Model	P100	P200	P300	P3100	P3500	P4300	P400	P500
Size Dimension H x W x D (mm)	42 x 187 x 115	42 x 229 x 127	38 x 145.5 x 90.5	44 x 430 x 250	44 x 430 x 250	54 x 430 x 258	216 x 375 x 152	108 x 877 x 115 Soundbar; 235 x 231 x 303 Subwoofer
Power (watts)	40 (8ohm, 20w x 2)	120 (8ohm, 60w x 2)	-	3 zones x 40 (8ohm, 20w x 2)	3 zones x 200 (4ohm, 100w x 2)	3 zones x 220 (4ohm, 110w x 2)	closed system	closed system
Generation D Energy-Efficient Amplifier	■	■	-	■	■	■	■	■
Texas Instruments PurePath™ Distortion Reduction	■	■	-	■	■	■	■	■
Digital Signal Optimization	■	■	■	■	■	■	■	■
Zone Grouping	■	■	■	■	■	■	■	■
Independent Zone Control	■	■	■	■	■	■	■	■
Apple / Android Control App	■	■	■	■	■	■	■	■
Internet Radio	■	■	■	■	■	■	■	■
Wi-Fi	■	■	■	-	-	-	■	■
Ethernet Connection	■	■	■	■	■	■	■	■
Line In/Out	■	■	■	■	■	■	■	■
Optical In/Out	-	-	■	-	-	-	-	-
USB Port	■	■	■	■	■	■	■	■
Bluetooth	-	■	-	-	-	-	-	-
ICEpower® audio technology	-	-	-	-	■	-	-	-