

Single Zone Players

All-In-One Speaker/Player

Multi-Zone Players

Din rail Player

									
Model	P100	P200	P300	P400	P500	P3100	P3500	P4300	P600
Size Dimension H x W x D	42 x 187 x 115 (mm) 1.65 x 7.36 x 4.5 (in)	42 x 229 x 127 (mm) 1.65 x 9 x 5 (in)	38 x 145.5 x 90.5 (mm) 1.5 x 5.7 x 3.56 (in)	216 x 375 x 152 (mm) 8.5 x 14.76 x 5.98 (in)	Sound Bar 108 x 877 x 115 (mm) 4.25 x 34.5 x 4.52 (in) Subwoofer 235 x 231 x 303 (mm) 9.25 x 9 x 11.9 (in)	44 x 430 x 250 (mm) 1.73 x 16.9 x 9.8 (in)	44 x 430 x 250 (mm) 1.73 x 16.9 x 9.8 (in)	54 x 430 x 258 (mm) 1.73 x 16.9 x 10.1 (in)	53.4 x 90 x 67.2 (mm) 2.102 x 3.543 x 2.646 (in)
Power (watts)	40 (8ohm, 20w x 2)	120 (4ohm, 60w x 2)	preamplifier	closed system	closed system	3 zones x 40 (8ohm, 20w x 2 per zone)	3 zones x 100 @ 8ohm (8ohm, 50w x 2 per zone)	3 zones x 110 @ 4, 6, or 8ohm (55w x 2 per zone)	40 (4, 6, or 8ohm, 20w x 2)
Generation D Energy-Efficient Amplifier	■	■	-	■	■	■	■	■	■
Domotz Ready	■	■	■	■	■	■	■	■	■
Apple / Android Control App	■	■	■	■	■	■	■	■	■
Wi-Fi	■	■	■	■	■	-	-	-	-
Ethernet Connection	■	■	■	■	■	■	■	■	■
Analog Line In	■	■	■	■	■	■	■	■	■
Analog Line Out	■	■	■	-	-	■	■	■	-
Optical In	-	-	■	-	■	-	-	■	-
Optical Out	-	-	■	-	-	-	-	■	-
USB Port	■	■	■	■	■	■	■	■	■
Bluetooth	-	■	-	-	-	-	-	-	-
ICEpower® audio technology	-	-	-	-	-	-	■	-	-
Four Ohm Stable	-	-	-	-	-	-	■	■	■
DSP	-	-	-	■	-	-	-	■	-
Trigger In	-	-	-	-	-	-	-	-	-
Trigger Out	-	-	-	-	-	■	■	■	-
Power-up Options	-	-	-	-	-	-	-	-	-