

HELPING CONTRACTORS, FACILITY MANAGERS AND HOMEOWNERS

WITH CODE-COMPLIANT PORTABLE GFCI SOLUTIONS.



FROM THE FIRST-EVER GFCI RECEPTACLES TO OUR LATEST PORTABLE SOLUTIONS, WE KEEP YOU SAFE ON THE JOB -ANYTIME, ANYWHERE.

## GFCI protection for any application.

In 1972, we introduced the very first GFCI receptacle. In the decades since, we've helped save lives, prevent injuries and protect spaces by continuing to innovate with our range of industry-leading GFCI solutions. This dedication to safety extends to our line of portable GFCIs. Preventing injury from electrical shock by interrupting power in the event of a ground fault, these rugged and portable devices are

perfect for a variety of temporary power applications, including use with power tools, high-pressure power washers, wet vacuums and grounds-keeping equipment, spas and hot tubs, vending machines, portable signs and more. Find reliable GFCI protection for any application, and easy compliance with National Electrical Code(R) (NEC) and OSHA Requirements, with Legrand's portable GFCI solutions.



- seconds, ensuring they are always ready to
- 1597 and 2097 models include a red indicator light which flashes red if the self-test fails to signal it should be replaced.
- 1597 and 2097 portable GFCIs include Safe-Lock protection. If critical components are damaged and ground fault protection is lost, power to the connected device is discon-
- Rugged polycarbonate housing stands up to impact and hard use.

- models).
- Automatic-reset models available for applications where continuous power is required (pumps, pressure washers, portable signs, lighting and engine heaters).
- Open neutral protection, standard on all models, automatically cuts off power to the hot conductor if there's a loss in continuity in the neutral conductor leading to the device.
- Choose from 15A and 20A models to meet virtually any portable GFCI application requirement.

## **In-Line Portable** Auto Reset GFCI

- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional Tri-Cord connector handles up to three loads.





1597CS1M

PL204L

			RATINGS		NEMA	CONFIGURATION	
CATALOG NO.	DESCRIPTION	RESET	A.	V.	CONFIG. NO.	PLUG	CONNECTION
RIGHT ANGLE PLUG — PORTABLE GFCI							
1597CMM	User attachable	Manual	15	125	5-15P		N/A
1597CMA	User attachable	Automatic	15	125	5-15P		
15 AMP IN-LINE — PORTABLE GFCI							
1597PC6M	6' cord, straight blade	Manual	15	125	5-15P/R		
1597PC2M	2' cord, straight blade	Manual	15	125	5-15P/R	الله الله	
1597PC2A	2' cord, straight blade	Automatic	15	125	5-15P/R		
1597TC2M	2' cord with tri-cord connector	Manual	15	125	5-15P/R		
1597TC2A	2' cord with tri-cord connector	Automatic	15	125	5-15P/R		
1597TL2M	2' cord, Turnlok <sup>°</sup>	Manual	15	125	L5-15P/R		
1597TL2A	2' cord, Turnlok	Automatic	15	125	L5-15P/R		(40)
20 AMP IN-LINE — PORTABLE GFCI							
2097PC2A	2' cord, straight blade	Automatic	20	125	5-20P/R		
2097PC2M	2' cord, straight blade	Manual	20	125	5-20P/R		(الم
2097TL2A	2' cord, Turnlok	Automatic	20	125	L5-20P/R	(t)	(aff of
2097TL2M	2' cord, Turnlok	Manual	20	125	L5-20P/R		(0)
CORD SET — PORTABLE GFCI							
1597CS1M	1' cord with connector	Manual	15	125	5-15P/R	( C     1	
1597CS1A	1' cord with connector	Automatic	15	125	5-15P/R		U Uw)
BOX UNIT — PORTABLE GFCI							
PS154S	Four 15A, 125V straight blade outlets; cord has 15A, 125V plug	Automatic	15	125	5-15P 5-15R		
PS204S	Four 20A, 125V straight blade outlets; cord has 20A, 125V plug	Automatic	20	125	5-20P 5-20R	To I	
PL204L	Two 20A, 125V straight blade outlets and one 20A, 125V locking outlet has 20A, 125V locking plug	Automatic	20	125	L5-20P L5-20R 5-20R	( <b>t</b> )	



c(UL)us All GFCIs are 3rd Party Compliant with UL943, UL498

designed to be better.



## Legrand, North America

60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

570 Applewood Crescent Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca