

More stimulus-compliant products from us, **more opportunities for you.**



Meet the demands of even the most challenging stimulus-funded projects.

As government stimulus spending continues to drive new construction, opportunities abound for electrical contractors. But, in order to take advantage of those stimulus dollars, everything you install must meet the stipulations set forth in the



Buy American provision of the American Reconstruction and Reinvestment Act [ARRA].*

That's why it's important to have a partner like Legrand/ Pass & Seymour. We offer the most comprehensive line of stimulus-compliant wiring products in the industry, with everything from our P&S PlugTail[™] devices to lighting controls, switches, receptacles and screwless wall plates manufactured right here in North America. In addition, we also offer a full line of products manufactured in free trade agreement member countries. That means, whatever the project, and whatever the application, Legrand/Pass & Seymour can help you reap the rewards of stimulus-funded public works opportunities.

* Section 1605 of the American Reconstruction and Reinvestment Act (ARRA), also known as the Buy American provision, requires that certain materials used in projects funded by the Act be manufactured in the US or in specific foreign countries signatory to the Free Trade Agreement (FTA) and the World Trade Organization (WTO) Agreement.













All specification-grade receptacles and switches, along with our full line of plugs, connectors, Flexcor[®] products and wall plates, are manufactured in stimulus-compliant countries. The part numbers shown represent products that may have more than one country of origin. We offer a non-NA part # for receptacles, switches, plugs and connectors, and wall plates that meet NAFTA standards — for more information, visit **legrand.us/passandseymour**.

P&S Stimulus-Compliant Commercial Products

P&S PlugTail™						3rd Party Compliance			
	Description	O slar	Rati	ngs	NEMA	ւ (ՍԼ) սs UL943	շ Ա ս։ ՍL498	FSUL WC596	
Catalog Number	Description	Color	Α.	V.	Config. No.	C22.2 No. 144	C22.2 No. 42	WC378	
Specification Grade Duplex GFCIs									
PT1595NA*	Decorator	I, W, LA, GRY	15	125	5-15R	•	•	•	
PT2095NA*	Decorator	I, W, LA, GRY, RED	20	125	5-20R	•	•	•	
PT2095TRNA*	Tamper-Resistant	I, W, LA, GRY	20	125	5-20R	•	•	•	
PT1595NTLTRNA*	Tamper-Resistant LED Nightlight Combination	I, W	15	125	5-15R	•	•	•	
PT2095NTLTRNA*			20	125	5-20R	•	•	•	
Hospital Grade Dup	lex GFCIs								
PT2095HGNA*	Decorator	I, W, LA, GRY, RED	20	125	5-20R	•	•	•	
PT2095HGTRNA*	Tamper-Resistant		20	125	5-20R	•	•	•	
PT1595HGNTLTRNA*	Tamper-Resistant LED	I, W	15	125	5-15R	•	•	•	
PT2095HGNTLTRNA*	Nightlight Combination	I, W, RED	20	125	5-20R	•	•	•	
P&S PlugTail Receptacle Right Angle Connectors									
PTRA6STRNA	6" Stranded THHN12								
PTRA6SOLNA	6" Solid THHN12								

P&S GFCIs					3rd Party Compliance			
Catalog Number			ngs	NEMA Config. No.	ւ(Ս) սո ՍԼ943	շ (Ս) սs UL498	FSUL WC596	
j	Description		Α.	٧.		C22.2 No. 144	C22.2 No. 42	
Hospital Grade Duplex GFCIs								
1595HGNA*	Decorator	I, W, —, LA, GRY, RED	15	125	5-15R	•	•	•
2095HGNA*			20	125	5-20R	•	•	•
2095HGTRNA*	Tamper-Resistant	I, W, LA, GRY, RED	20	125	5-20R	•	•	•
	Catalog Number Hospital Grade Dup 1595HGNA* 2095HGNA*	Catalog Number Description Hospital Grade Duplex GFCIs 1595HGNA* 2095HGNA*	Catalog Number Description Color Hospital Grade Duplex GFCIs 1595HGNA* Decorator 2095HGNA* Decorator I, W, -, LA, GRY, RED	Catalog Number Description Ratin Hospital Grade Duptex GFCIs A. 1595HGNA* Decorator 15 2095HGNA* I, W, -, LA, GRY, RED 15	Catalog Number Description Ratings Hospital Grade Duplex GFCls A. V. 1595HGNA* Decorator 15 125 2095HGNA* A V. 125	Catalog Number Description Color Ratings NEMA Config. No. Hospital Grade Duplex GFCIs I. V. V. V. 1595HGNA* Decorator I, W, -, LA, GRY, RED 15 125 5-15R 2095HGNA* V. V. V. V. V. V.	Pack OF C1S Pack OF C1S	Pack OF C1S Pack OF C1S

P&S Lighting Co	ontrols							
Catalog Number	Description	Ratings	Color					
P&S Titan [™] Series Fluorescent Dimmers								
CD3FB10277NA*	3-Wire Electronic, Single-Pole, Slide-to-OFF	277V, 10A						
CD3FB103P277NA*	3-Wire Electronic, Single-Pole/3-Way, Preset	277V, 10A						
CD3FB163PNA*	3-Wire Electronic, Single-Pole, Slide-to-OFF	120V, 16A						
CD4FBNA*	Slide-to-OFF, Single-Pole, Electronic, 4-Wire	24VDC						
CD4FB3PNA*	Slide-to-OFF, Single-Pole/3-Way Electronic, 4-Wire	24VDC						
CDFB103PNA*		5A, 120V						
CDFB103P277NA*		10A, 277V						
CDFB163PNA*	2-Wire Electronic, Single-Pole/3-Way	16A, 120V	—— I, WH					
CDFB73P277NA*		7A, 277V						
CDFB83PNA*		8A, 120V						
CDFB5NA*	2-Wire Electronic, Single-Pole, Slide-to-OFF	5A, 120V						
CDFB53NA*	2-Wire Electronic, Single-Pole/3-Way, Preset	5A, 120V						
CDFB7277NA*	2-Wire Electronic, Single-Pole, Slide-to-OFF	7A, 277V						
CDFB73P277NA*	2-Wire Electronic, Single-Pole/3-Way, Preset	7A, 277V						
P&S Titan [™] Series	Dimmers							
CD703PNA*	-	120V, 700W						
CD1103PNA*	Single-Pole/3-Way, Preset	120V, 1100W	— і. wн					
CD1603PNA*	Single-Pole/S-Way, Presel	120V, 1600W	1, ****					
CD2003PNA*		120V, 2000W						
P&S Titan [™] Series Low Voltage Dimmers								
CDLV1103PNA*	Single-Pole/3-Way, Preset	120V, 1100W	I, WH					
P&S Titan [™] Series Fan Speed Controls								
CDSC6NA*	Continuously Variable Speed Fan Speed Control	120V, 6A	I, WH					
CDDH16NA*	Dehummer, 4-Speed, Fan Speed Control	120V, 1.6A	I, WO					

P&S Stimulus-Compliant Wiring Devices

P&S Recepta	P&S Receptacles, GFCIs and Power Outlets					3rd Party Compliance		
Catalog Number	Description		Ratings		NEMA Config. No.	cUL943 C22.2 No.	¢Այս։ UL498 C22.2 No.	FSUL WC596
			Α.	٧.	-	144	42	
Specification Grade Tamper-Resistant Receptacles								
3232TRNA*	Duplex	I, W, —, BK, LA	15	125	5-15R		•	
885TRNA*	Decorator	I, W, GRY, LA	15	125	5-15R		•	
885TR*	Decorator	—, ВК	15	125	5-15R		•	
Specification Grade GFCIs								
1595NA*	Duplex		15	125	5-15R	•	•	•
2095TRWRNA	Decorator	- I, W, —, GRY, BK, LA	20	125	5-20R	•	•	•
Specification Gr	Specification Grade Tamper-Resistant GFCIs							
1595TRNA*	Duplex	- I, W, —, GRY, BK, LA	15	125	5-15R	•	•	•
2095TRNA*	Decorator	1, W, —, GRY, BK, LA	20	125	5-20R	•	•	•
Specification Gr	Specification Grade Tamper-Resistant Weather-Resistant GFCIs							
1595TRWRNA	Duplex	I, W, —, LA	15	125	5-15R	•	•	•
2095TRWRNA	Duplex	I, W, —, GRY, LA	20	125	5-20R	•	•	•
Power Outlet Receptacles								
3884NA	3-Pole, 4-Wire	Grounding Surface Receptacle, Dryer	30	125/250	14-30		•	
3864NA	3-Pole, 4-Wire	Grounding Flush Receptacle, Dryer	30	125/250	14-30		•	
3854NA	3-Pole, 4-Wire	Grounding Surface Receptacle, Range	50	125/250	14-50		•	
3894NA	3-Pole, 4-Wire	Grounding Flush Receptacle, Range	50	125/250	14-50		•	

P&S Stimulus-Compliant Residential Products

_	D&S Switches 3rd Party Compliance								
	P&S Switches	2&S Switches							
	Catalog Number	Description	Color		ngs	(UL 20			
	Catalog Number	Description		Α.	۷.	C22.2 No. 111			
	TradeMaster® Toggle Switches								
	660NA*G	Single-Pole	I, W, —, BK, LA1		120	•			
	663*G	3-Way		15		•			
	664*G	4-Way				•			
	TradeMaster® Decorator Switches								
	TM870NA*	Single-Pole	 I, W, —, GRY, BK, LA		120	•			
	TM873NA*	3-Way		15		•			
	TM874*	4-Way				•			

P&S Lighting Controls								
Catalog Number	Description	Ratings	Color					
P&S Harmony [™] Dimmers and Fan Speed Controls								
D703PNA*	Incondessont Cingle Data and 2 Wey	120V, 700W	I. WH					
D1103PNA*	Incandescent Single-Pole and 3-Way	120V, 1100W						
DDH16PNA*	Dehummer Fan Speed Control	120V, 1.6A						
	*Color I Ivory	W White GRY Gray	BK Black					

C Clear

Designation

designed to be better.™

For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/PassandSeymour. We're eager to put our expertise to work for you.

Distributed by:

Legrand, North America

RED Red

60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

570 Applewood Crescent Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca

Llegrand[®]

Light Almond

LA

Legrand/Pass & Seymour P.O. Box 4822 Syracuse, NY 13221-4822 800.776.4035 www.legrand.us/PassandSeymour

Brown

Follow Us