

**Exceptional strength and durability
in severely corrosive environments.**

CGSS Series



Pass & Seymour corrosion-resistant cord connectors feature a body and compression nut made of Type 304 stainless steel with exceptional tensile strength and the highest levels of durability in severely corrosive environments. All stainless steel cord grips include an embedded Buna-N O-Ring. These connectors are recommended for use in washdowns or high-moisture environments in food processing plants, petrochemical facilities, wastewater treatment plants, pulp and paper mills and chemical manufacturing factories.

[Note: Type 316 stainless steel also available upon request and minimums may apply.)

Features & Benefits



Stainless Steel Deluxe Cord Grip

- **304 grade Stainless Steel construction** provides exceptional tensile strength and resists corrosion and impacts
- **Includes an embedded Buna-N O-Ring** providing a long-term seal and protection against ingress
- **The combination tightening surface** provides a large wrenching area for easy installation
- **Available in** straight male from 3/8" to 3" NPT
- **Also available in** 316 grade stainless steel, upon request. Minimums may apply.

3rd Party Compliance



Most Flexcor products have UL and/or CSA approvals. Please consult factory for approval information. Conforms to NEMA 3R.

HAZARDOUS LOCATIONS

Definition	Legrand Products
The Legrand products listed are suitable for use in hazardous locations per Class I, Div. 2; Class II, Div. 1 & 2; and Class III, Div. 1 & 2	CG Series – Straight, 90°, 45° CGSS Series – Straight CGSS-M Series – Straight

Ordering Information

Deluxe Stainless Steel Cord Grips

Catalog Number Cord Grip	Cable Diameter Range
3/8" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS38188	0.120" - 0.180"
CGSS38250	0.180" - 0.250"
CGSS38312	0.250" - 0.310"
CGSS38375	0.310" - 0.370"
CGSS38438	0.370" - 0.430"
1/2" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS50188	0.120" - 0.180"
CGSS50250	0.180" - 0.250"
CGSS50312	0.250" - 0.310"
CGSS50375	0.310" - 0.370"
CGSS50438	0.370" - 0.430"
CGSS50500	0.430" - 0.500"
CGSS50562	0.500" - 0.560"
CGSS50625	0.560" - 0.620"
3/4" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS75500	0.430" - 0.500"
CGSS75562	0.500" - 0.560"
CGSS75625	0.560" - 0.620"
CGSS75688	0.560" - 0.680"
CGSS75750	0.620" - 0.750"
CGSS75812	0.680" - 0.810"
1" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS1001000	0.870" - 1.000"
CGSS100562	0.440" - 0.560"
CGSS100625	0.560" - 0.620"
CGSS100688	0.560" - 0.680"
CGSS100750	0.620" - 0.750"
CGSS100812	0.680" - 0.810"
CGSS100875	0.750" - 0.870"
CGSS100938	0.810" - 0.930"
1 1/4" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS1251000	0.870" - 1.000"
CGSS1251125	1.000" - 1.120"
CGSS1251250	1.120" - 1.250"
CGSS1251375	1.250" - 1.370"
CGSS125688	0.560" - 0.680"
CGSS125812	0.680" - 0.810"
CGSS125875	0.750" - 0.870"

Deluxe Stainless Steel Cord Grips

Catalog Number Cord Grip	Cable Diameter Range
1 1/2" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS1501000	0.870" - 1.000"
CGSS1501125	1.000" - 1.120"
CGSS1501250	1.120" - 1.250"
CGSS1501375	1.250" - 1.370"
CGSS150688	0.560" - 0.680"
CGSS150812	0.680" - 0.810"
CGSS150875	0.750" - 0.870"
2" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS2001375	1.250" - 1.370"
CGSS2001562	1.430" - 1.560"
CGSS2001688	1.560" - 1.680"
CGSS2001812	1.680" - 1.810"
CGSS2001938	1.810" - 1.940"
CGSS2002062	1.940" - 2.060"
CGSS2002188	2.060" - 2.190"
CGSS2002312	2.190" - 2.310"
CGSS2002438	2.310" - 2.440"
2 1/2" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS2501812	1.680" - 1.810"
CGSS2501938	1.810" - 1.940"
CGSS2502062	1.940" - 2.060"
CGSS2502188	2.060" - 2.190"
CGSS2502312	2.190" - 2.310"
CGSS2502438	2.310" - 2.440"
3" Stainless Steel 304 IP 67 68 Cord Grip	
CGSS3002635	2.440" - 2.630"
CGSS3002812	2.630" - 2.810"
CGSS3003000	2.810" - 3.000"
CGSS3003250	3.000" - 3.250"



Stainless Steel Deluxe Cord Grip

Country of Origin: United States

Most Flexcor products have UL and/or CSA Approvals.
Please contact factory for approval information.


All devices listed on this page meet NEMA 3R standards.

Field Uses/Vertical Markets

- Temporary Power
- Industrial Manufacturing
- Maintenance Repair Operations
- Panel Building
- Utilities
- Renewable Energy

Also available...

- Hospital Grade Devices
- PlugTail® Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Portable GFCIs

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

