



For accurate, faster jobs that require significantly less labor, choose from a wide variety of PlugTail Connectors designed specifically to work with our PlugTail line of receptacles, switches, and sensors. With an array of lengths and connector types that cover a multitude of on-site and prefab needs, experience the ease and efficiency of using PlugTail devices on your next project, like so many successful installations before you. Color options and push-in connectors help you finish projects in record time.

Feature & Benefits:

- Large crimped and welded brass contacts snugly terminate on device blade terminals.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger-safe housing.
- Audible snapping latch assures connection, allows release.
- Exclusive patented feature, circuit label on back allows permanent circuit identification.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Boost productivity even more with special add-ons: 4-port push-in connectors, fork terminal on ground wire, colored connector heads and longer-length pigtail solutions.
- No exposed terminals create a finger-safe application before, during, and after installation.
- Right-angle connectors fit flush with device back to leave more room in box
- Switch connectors offer 3-wire solution for single pole, 4-wire solutions for 3-way applications.
- WAGO push-in connectors are available to further speed up installation.



PTRA6STRBP



PTS6SOL4



PTRA6STRNA



PTRA6SOLNA

Catalog #	Device Type	Wire Type	Length of Lead	Packaging Style	Special Feature
PTRA6SOL	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTRA6SOLB12	Receptacle	#12 AWG Solid THHN	12 in.	To be determined	Pre-stripped pigtail leads
PTRA6SOLB25	Receptacle	#12 AWG Solid THHN	25 in.	To be determined	Pre-stripped pigtail leads
PTRA6SOLBP	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTRA6SOLG	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; Fork terminal pre-installed on ground wire
PTRA6SOLNA	Receptacle	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; NAFTA Compliant
PTRA6STR	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTRA6STRB12	Receptacle	#12 AWG Stranded THHN	12 in.	To be determined	Pre-stripped pigtail leads
PTRA6STRB180	Receptacle	#12 AWG Stranded THHN	15 ft.	To be determined	Pre-stripped pigtail leads
PTRA6STRB25	Receptacle	#12 AWG Stranded THHN	25 in.	To be determined	Pre-stripped pigtail leads
PTRA6STRBP	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTRA6STRG	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; Fork terminal pre-installed on ground wire
PTRA6STRNA	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; NAFTA Compliant
PTRA6STRNABL	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; blue connector base for UPS and Surge Protective applications
PTRA6STRNARED	Receptacle	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; red connector base for emergency circuit applications
PTRA6STRXBB	Receptacle	#12 AWG Stranded XHHW	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL3	1P Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL3277	1P, 277-Volt Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL3BP	1P Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6SOL4	3W Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL4277	3W, 277-Volt Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6SOL4BP	3W Switch	#12 AWG Solid THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR3	1P Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR3277	1P, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR3277BP	1P, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR3BP	1P Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR4	3W Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR4277	3W, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads
PTS6STR4277BP	3W, 277-Volt Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires
PTS6STR4BP	3W Switch	#12 AWG Stranded THHN	6 in.	25 ct. Box	Pre-stripped pigtail leads; 4-port push-in connectors on all 3 wires



©2017 Legrand All Rights Reserved. SS1920 12/17

designed to be better.™



PTS6STR4BP



PTS6SSTR3BP



PTS6STR3



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 132214822
800.776.4035
www.legrand.us

Canada
9024 Keele Street,
Vaughan, Ontario L4K 2N2
www.legrand.ca

FOLLOW US

