



Features & Benefits


PASS & SEYMOUR® Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs 15 & 20A, 125VAC

Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs offer superior durability and protection.

1597HGTRWR* (W, I, LA, BK, GRY, RED) 2097HGTRWR* (W, I, LA, BK, GRY, RED)

The new Pass & Seymour[®] Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCI receptacle with SafeLock[®] Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For non-Hospital Grade, refer to SF1101R6.



3rd Party Compliance



cULus Listed File Number E42190, Standard UL498 Attachment Plugs and Receptacles, UL943 GFCIs. **US LISTED** Federal Specification WC596, Hospital Grade. Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.




PASS & SEYMOUR® Hospital Grade Tamper-Resistant Weather-Resistant

Self-Test GFCIs 15 & 20A, 125VAC

Technical Information

Performance		
Electrical		
Dielectric Voltage	Withstands 1500V minimum	
Trip Level	4 to 6 mA	
Trip Time	.025 Second Nominal	
Frequency	60 Hz	
Maximum Working Voltage	125VAC	
Voltage Range	102-132VAC	
Mechanical		
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)	
Terminal Accommodation	#14 AWG – #10 AWG solid or stranded copper conductor only	
Product Identification	Ratings are a permanent part of the device	
Environmental		
Flammability	UL94 V2	
Operating Temperature	-35°C to +66°C	
Maximum Humidity	95%	



Dimensions for 15 & 20 Amp

Hospital Grade TR WR GFCI Receptacle Materials

-	-	
Face	UV-Resistant Nylon	
Body	Nylon	
Contacts	.03" Brass (.8)	
Mounting Straps	Galvanized Steel	
Terminal Screws	Nickel-Plated Steel #8 - 32	
Hex Head Grounding Screw	Nickel-Plated Steel with Green Paint	
Mounting Screws	Zinc-Plated Steel with Black Chromate	
Test/Reset Buttons	UV-Resistant Nylon	
Tamper-Resistant Shutter	Thermoplastic	


Warranty


1 Year



Ordering Information

Catalog Number	Description		g V	NEMA Configuration No.	
1597HGTRWRW	Description	A 15A	125V	Color White	5-15R
1597HGTRWRI	Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs	15A	125V	lvory	5-15R
1597HGTRWRLA		15A	125V	Light Almond	5-15R
1597HGTRWRBK		15A	125V	Black	5-15R
1597HGTRWRGRY		15A	125V	Gray	5-15R
1597HGTRWRRED		15A	125V	Red	5-15R
2097HGTRWRW	Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs	20A	125V	White	5-20R
2097HGTRWRI		20A	125V	lvory	5-20R
2097HGTRWRLA		20A	125V	Light Almond	5-20R
2097HGTRWRBK		20A	125V	Black	5-20R
2097HGTRWRGRY		20A	125V	Gray	5-20R
2097HGTRWRRED		20A	125V	Red	5-20R





SF20235 — April 2018 — For latest specs visit www.legrand.us/passandseymour



PASS & SEYMOUR®

Hospital Grade Tamper-Resistant Weather-Resistant Self-Test GFCIs 15 & 20A, 125VAC

Vertical Markets

• Industrial • Retail	 Healthcare Office 	 Education Hospitality/Lodging 	 Institutional Multiple Dwelling
Also available			
 USB Charging Devices PlugTail[®] Devices SPD & Isolated Ground Devices 	 Ground Continuity Monitoring Devices (GCM) Straight Blade Plugs & Connectors Turnlok[®] Locking Devices 	 Weatherproof Boxes and Covers IEC 309 Industrial Products 	 Flexcor[®] Wire Mesh Grips Night Lights

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us 905.738.9195 www.legrand.ca

