
WALL PLATES & SPECIALTIES

RWP26LA

radiant™ Screwless Polycarbonate Wall Plates

- **A. Redesigned screwless wall plates** feature a lower, more modern profile in keeping with today's design trends.
- B. Molded of rugged .065" thick polycarbonate.
- **C. One-piece subplate** mounts over the device for easy retrofit and lower profile.
- **D. Subplate screws align devices** to ensure proper positioning of wall plates.
- E. Opening accommodates all NEMA 26-opening devices.
- F. An extra 3/8" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.



RWP26LA

The radiantTM collection is a step up from the standard with simple, classic options in wiring devices, home automation controls, and screwless wall plates that complement today's homes and hospitality settings.

Specifications



radiant™ Screwless Polycarbonate RWP Series



Thermoset SP Series



Nylon TP Series



302/304 Stainless Steel



Polished Brass



Brushed Brass



Aluminum

Application

Legrand's broad line of Pass & Seymour® Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour devices.

Screwless Polycarbonate Wall Plates

- Part of the radiant™ collection.
- Molded of .065" thick polycarbonate, matte finish.
- One-piece subplate mounts over the device for easy retrofit and lower profile.
- Extra 3/8" width and height than Standard size plates.
- Available in Ivory, White, Brown, Gray, Black, and Light Almond; and three metallic finishes – nickel, dark bronze, antique brass.

Thermoset Plastic Wall Plates

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

TradeMaster® Thermoplastic Wall Plates

- Molded of rugged, practically indestructible self-extinguishing nylon. ["TP" series only]
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"


Metal Wall Plates

- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze or galvanized steel
- Standard, Jumbo, and Tandem size plates available, as well as special Panel size plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes. Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Materials

- Type 302/304 Stainless Steel, non-magnetic, .032" nominal thickness, brushed finish. This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Type 430 Stainless Steel, magnetic, .032" nominal thickness, brushed finish. Less corrosion-resistant than Type 302/304, but ideal for general service in high abuse applications in industrial plants, commercial, and institutional buildings.
- Chrome, Brushed and Polished Brass, .040" thick. 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications. Lacquered to prevent corrosion.
- Aluminum, .040" thick. Lustrous satin finish. Lacquered to prevent corrosion.
- Galvanized Steel. Used only for Handy Box Plates
- Brushed Bronze, .040" thick. 90% copper, 10% zinc. Lacquered to prevent corrosion.

Dimensions



Standard Size Wall Plates

- Standard size wall plates for all applications.
- Best fit for surface mount boxes.
- Available in plastic and metal only.

Dimensions

1 gang 2.75" x 4.5" 2 gang 4.56" x 4.5" 3 gang 6.375" x 4.5" 4 gang 8.125" x 4.5" 5 gang 10" x 4.5" 6 gang 11.812" x 4.5" 13.62" x 4.5" 7 gang 15.44" x 4.5" 8 gang

TradeMaster® Wall Plates

- Extra 3/16" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle and 26-style single gang plates.

Dimensions

1 gang 2.9375" x 4.6875"
2 gang 4.75" x 4.6875"
3 gang 6.563" x 4.6875"
4 gang 8.375" x 4.6875"
5 gang 10.188" x 4.6875"
6 gang 12" x 4.6875"

radiant™ Screwless

Polycarbonate Wall Plates

- Available in 26-style openings.
- Extra 3/8" width and height than Standard size wall plates.
- Provide better sheet rock coverage with standard size appearance.
- Molded of .065" thick polycarbonate.
- 2-piece plastic subplate made of polycarbonate.
- Available in 3 metallic finishes and 6 standard colors.

Wall Plate Dimensions

1 gang 3.15" x 4.94" 2 gang 4.96" x 4.94" 3 gang 6.77" x 4.94" 4 gang 8.59" x 4.94" 5 gang 10.40" x 4.94" 6 gang 12.21" x 4.94"

Subplate Dimensions

1 gang 1.81" x 4.78" x .15"
2 gang 3.62" x 4.78" x .15"
3 gang 5.44" x 4.78" x .15"
4 gang 7.25" x 4.78" x .15"
5 gang 9.06" x 4.78" x .15"
6 gang 10.87" x 4.78" x .15"

Junior-Jumbo Wall Plates

- Extra 3/8" width and height than Standard size wall plates.
- Additional coverage for sheet rock gaps.
- · Available in plastic and metal only.

Dimensions

1 gang 3.125" x 4.87" 2 gang 4.93" x 4.87" 3 gang 6.75" x 4.87" 4 gang 8.56" x 4.87"

TradeMaster® Jumbo Wall Plates

- Extra 3/16" width and height than Junior-Jumbo size wall plates.
- Provide additional coverage for sheet rock gaps, matching the appearance of the TradeMaster Plates.
- Available in unbreakable nylon 6 construction only.
- Screws pre-installed in the duplex, toggle, and 26-style single gang plates.

Dimensions

1 gang 3.3125" x 5.0625" 2 gang 5.125" x 5.0625" 3 gang 6.9375" x 5.0625" 4 gang 8.75" x 5.0625"

Jumbo Wall Plates


- Extra 3/4" width and height than Standard size wall plates.
- Largest size wall plates to cover larger wall damage.
- Available in plastic and metal only.

Dimensions

1 gang 3.5" x 5.25" 2 gang 5.31" x 5.25" 3 gang 7.12" x 5.25" 4 gang 8.93" x 5.25"



Dimensions




Sectional Wall Plates

End and center panels with each of five most-used configurations make it possible to improvise custom wall plates on the job. Panels lock securely together on installation. Blank sections furnished with mounting strap.


Wall Plate Mountings

Illustrated are the five standard methods of plate mounting. There are many other non-standard methods which depend upon the special device used. Exact mounting hole specifications for every device appear in the Selector Guide.





Wall Plate Sizes


Standard SizeAvailable in plastic and metal




1.8125









TradeMaster® Size







Tandem Wall Plates




Metal only. Plate mounting dimensions are non-standard. Refer to Page P-26 for details and devices that can be used.

For radiant™ Screwless (RWP) Wall Plate dimensions refer to Page P-4.




radiant™ Metallic Finish Screwless Wall Plates Polycarbonate



For Screwless Wall Plate and Plastic Subplate dimensions, see Pages P-4 and P-5.




radiant™ Screwless Wall Plates Polycarbonate



One Gang	Two Gang	Three Gang	Four Gang
		55 549	

		26 OPENINGS			
DESCRIPTION	COLOR				
SCREWLESS W	SCREWLESS WALL PLATES PLASTIC S				
One Gang	lvory	RWP26I			
	White	RWP26W			
	Brown	RWP26			
	Gray	RWP26GRY			
	Black	RWP26BK			
	Light Almond	RWP26LA			
Two Gang	lvory	RWP262I			
	White	RWP262W			
	Brown	RWP262 RWP262GRY			
	Gray Black	RWP262BK			
	Light Almond	RWP262LA			
Three Gang	lvory	RWP263I			
	White	RWP263W			
	Brown	RWP263			
	Gray	RWP263GRY			
	Black	RWP263BK			
	Light Almond	RWP263LA			
Four Gang	lvory	RWP264I			
	White	RWP264W			
	Brown	RWP264			
	Gray	RWP264GRY			
	Black	RWP264BK			
Fine One	Light Almond	RWP264LA RWP265I			
Five Gang	lvory White	RWP265I RWP265W			
	Brown	RWP265			
	Gray	RWP265GRY			
	Black	RWP265BK			
	Light Almond	RWP265LA			
Six Gang	lvory	RWP266I			
	White	RWP266W			
	Brown	RWP266			
	Gray	RWP266GRY			
	Black	RWP266BK			
	Light Almond	RWP266LA			



One Gang Two Gang
Plastic Subplate Plastic Subplate

DESCRIPTION	HEIGHT	WIDTH			
SCREWLESS 26 OPENINGS PLASTIC SUBPLATE INCLUDED					
One Gang	4.94"	3.15"			
Two Gang	4.94"	4.96"			
Three Gang	4.94"	6.77"			
Four Gang	4.94"	8.59"			
Five Gang	4.94"	10.40"			
Six Gang	4.94"	12.21"			

DESCRIPTION	HEIGHT	WIDTH			
SCREWLESS PLASTIC SUBPLATE DIMENSIONS					
One Gang	4.78"	1.81"			
Two Gang	4.78"	3.62"			
Three Gang	4.78"	5.44"			
Four Gang	4.78"	7.25"			
Five Gang	4.78"	9.06"			
Six Gang	4.78"	10.87"			