

RAPIDRUN PRODUCT COMPARISON

	RapidRun® Optical	RapidRun Digital		RapidRun Multi-Format		RapidRun Multi-Format Upgrade Kit	RapidRun PC Upgrade Kit
							
Color Code	Platinum	Red		Orange		Orange	Yellow
Signal Types	HDMI DVI DisplayPort	HDMI DVI Stereo Audio		VGA Composite Video Stereo Audio Component Video RGBHV Video DVI-A Video Serial RS232		HDMI	HDMI
Maximum Distance	1000ft	100ft		150ft		100ft	100ft
Length Increments	35ft, 50ft, 65ft, 80ft 100ft, 125ft, 150ft 175ft, 200ft, 500ft 750ft, 1000ft	CL2 6ft, 10ft, 15ft, 25ft, 35ft, 50ft, 65ft, 75ft, 100ft	Plenum 15ft, 25ft 35ft, 50ft 65ft, 75ft 100ft	CMG 6ft, 10ft 15ft, 25ft 35ft, 50ft 75ft, 100ft 125ft, 150ft	Plenum 15ft, 25ft 35ft, 50ft 75ft, 100ft 125ft, 150ft	—	—
Maximum Resolution	4k (4096x2160)	1080p (1920x1080)		1600x1200		1920x1200	1920x1200
Jacket Rating	Plenum, OFNP	In-wall, CL2 Plenum, CMP		In-wall, CMG Plenum, CMP		—	—
Additional Requirements	—	—		—		Requires an existing RapidRun Multi-Format Runner	Requires an existing RapidRun PC Runner
Install Type	New building construction	New building construction		New building construction		Room retrofits	Room retrofits
Best Applications	HDMI, DVI or DisplayPort laptop HDMI, DVI or DisplayPort projector Digital A/V signal support requirement High bandwidth requirement 4k resolution support requirement 3D video support requirement Deep Color support requirement	HDMI or DVI laptop HDMI or DVI projector Digital support requirement		VGA laptop Composite Video DVD player VGA and Composite projector		HDMI laptop or Blu-ray player VGA projector Existing RapidRun Multi-Format installation	HDMI laptop or Blu-ray player VGA projector Existing RapidRun Multi-Format installation