



## PADDLE™ SWITCH, 277V, MAGNESIUM

ASPD1532M277 | [adorne](#)

### FEATURES & BENEFITS

#### USAGE

- Perfect for anywhere you'd like to upgrade the look of a standard switch.
- With a classic up-and-down motion, the adorne Paddle Switch lets you turn lights on and off with ease.
- Use on its own to control a light from one location (single-pole operation) or pair with a second switch or dimmer to control a single light source from two locations (three-way operation).
- Pair with matching Paddle Dimmer Switch or **Paddle Fan Speed Control** to create a uniform look throughout a room or your entire house.
- This item also comes in and 20A and 20A 4-Way options.
- This item is also available in white and graphite.

#### GETTING STARTED

- Time to install: 15 minutes or less.
- Fits existing electrical box and does not require new wires for typical installation.
- Innovative snap-in system ensures easy installation.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.

### SPECIFICATIONS

#### GENERAL INFO

Color: Magnesium  
Product Series: adorne Paddle Switch  
Number Of Poles: Single Pole/3-Way  
Style: Paddle

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

ETL Listing No: Yes  
UL Standard: Yes

#### DIMENSIONS

Depth (US): 1.5"  
Length (US): 1.77"  
Width (US): 1.77"

## TECHNICAL INFORMATION

Amps: 15A

Volts: 120/278