



## SOFTAP™ WI-FI READY MASTER DIMMER, TRU-UNIVERSAL, MAGNESIUM

ADTP700RMTUM1 | [adorne](#)

### FEATURES & BENEFITS

#### USAGE

- Perfect anywhere you'd like to combine Wi-Fi-Ready lighting control with sensitive softTap technology and the option to dim.
- The softTap Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adorne Hub to create smart lighting solutions for your home.
- Turn lights on and off or dim with just the light tap of a finger – or create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- Compatible with the Google Assistant and Amazon Alexa
- This item is also available in white.

#### GETTING STARTED

- Time to install: 25 minutes or less.
- Easily install this Master dimmer into an existing electrical box and wire directly to the light.
- Once the Master dimmer is installed, a softTap Wi-Fi Ready Remote Dimmer may be installed to allow for Wi-Fi Ready control of a light from two locations without rewiring. Simply follow the instructions after installing to pair with the Master dimmer.
- Innovative snap-in system ensures easy installation.
- This item uses patented Tru-Universal technology, enabling the dimmer to support all load types including incandescent/halogen, magnetic low voltage (MLV), electronic low voltage (ELV) in forward or reverse phase, CFL/LED, etc.(with the exception of 0-10V LED drivers)
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the adorne Hub. [Shop now](#) to learn how Wi-Fi ready lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: Magnesium  
Product Series: adorne softTap  
Style: SofTap

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes  
FCC Standard: Yes  
UL Listing No: UL 1472  
UL Standard: Yes  
UN SPSC: 39112401

#### **DIMENSIONS**

Depth (US): 1.79"  
Height (US): 4.185"  
Length (US): 4.20"  
Width (US): 1.77"  
Product Weight (US): 0.32 pounds

#### **TECHNICAL INFORMATION**

AC Voltage Output: 120VAC  
Frequency: 900 MHz (RF)  
Humidity: 0-80% relative humidity, noncondensing  
Load: Incandescent, Halogen, MLV, Fluorescent, and ELV, CFL, and LED bulbs  
Material: FR4(PCB)  
Mounting: USA Electrical Wiring Box / adorne Mounting Plate  
Operating Temperature (Celsius): 0°C to 50°C  
Storage Temperature: 32°F to 122°F  
Watts: 700W Load Dependent