



TOUCH™ WI-FI READY REMOTE SWITCH, MAGNESIUM

ASTHRRM1 | [adorne](#)

FEATURES & BENEFITS

USAGE

- Perfect anywhere you'd like to combine Wi-Fi-Ready lighting control with sleek, recognizable touch technology.
- The Touch Wi-Fi Ready Remote Switch is a programmable light switch that pairs with the adorne Hub and the Touch Wi-Fi Ready Master Switch to create smart lighting solutions for your home.
- Turn lights on and off with the touch of a finger – or create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app.
- Compatible with the Google Assistant and Amazon Alexa
- This item is also available in white and graphite.

GETTING STARTED

- Time to install: 25 minutes or less.
- The Touch Wi-Fi Ready Remote Switch lets you control a light from a new location without running new wires. Simply install and pair with the Touch Wi-Fi Ready Master Switch via the easy-to-follow instructions and enjoy customizable control of a single lighting source from two locations or your smartphone.
- The Legrand Lighting Control app is available for free on iTunes and Google Play.
- This item requires the [adorne Hub](#). Shop now to learn how Wi-Fi lighting solutions can transform your home.
- This item requires an adorne Wall Plate. [Shop now](#) to choose from dozens of finishes including a variety of luxurious metals, or order in your own custom finish.
- Looking to integrate other party advanced automation systems? Visit our [partners page](#).

SPECIFICATIONS

GENERAL INFO

Color: Magnesium
Product Series: adorne Touch Dimmer
Style: Touch

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes
FCC Standard: Yes
UL Listing No: UL 508
UL Standard: Yes

UN SPSC: 39121107

DIMENSIONS

Depth (US): 1.63"

Height (US): 4.185"

Length (US): 2.66"

Width (US): 1.77"

Product Weight (US): 0.18 pounds

TECHNICAL INFORMATION

AC Voltage Output: 120VAC

Frequency: 900 MHz (RF)

Humidity: 0-80% relative humidity, noncondensing

Material: FR4(PCB)

Mounting: USA Electrical Wiring Box / adorne Mounting Plate

Operating Temperature (Celsius): 0°C to 50°C

Storage Temperature: 32°F to 122°F

Volts: 120

Watts: Auxiliary Remote - No Load