



CABLOPORTBASE WITH FAS P OR STRUT SUPPORT

CPP | [Cablofil](#)

FEATURES & BENEFITS

Cablo-Port is a UV and Weather resistant rubber base that creates a cushion between rooftop mounted equipment and sensitive roofing materials. Available in two styles, the Standard style is perfect for smaller loads and tight spaces and the Widebody design provides a broad base to minimize roof pressure and a larger area for glue application. Cablo-Port is also available with a wide variety of pre-mounted support options, including FAS P and Channel.

- **Flat roof support:** For support of tray, piping or other items on flat roofs.
- **Two support styles:** FAS Profile for wire mesh trays or 13/16" galvanized channel (14 ga.) for ladder tray, piping or other material support.
- **Install:** on any roofing material or other flat surface.
- **Supports are available in:** one standard finish and two optional finishes.
- **Curb style maximum load:** 750 lbs. (CPP5 and CPS5 - maximum load 200 lbs.).
- **Two rubber base designs:** Standard Curb and Widebody style
- **Widebody design:** has 1,000 lbs/ft maximum load and provides 5 times the surface area to minimize roof material pressure, increase load capacity and provide over 120 square in/ft for glue application.

SPECIFICATIONS

The below "View Specifications Chart" highlights all sizes and finishes available.

GENERAL INFO

Product Series: CabloPort

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CANADA