

---

## HAMMER-ON CONDUIT-TO-FLANGE BEAM CLAMPS, PUSH IN CONDUIT

CCP858B | [Cablofil](#)

---

### FEATURES & BENEFITS

Most of our conduit clamps feature a pre-galvanized, spring steel design with self-locking jaws that secure conduit to strut, metal studs, I-beams and drop wires. Many of those clamps hammer on with the need for additional hardware. Other clamps feature a setscrew and saddle to attach conduit to cable trays. Every Legrand clamp is designed to install with speed and efficiency and are boxed in quantity.

**CCP858B:** Conduit to Flange Clip, 1/2" EMT, 5/16"-1/2" Flange.

**CCP12912B:** Conduit to Flange Clip, 3/4" EMT, 1/2" Rigid, 9/16"-3/4" Flange.

**CCP824B:** Conduit to Flange Clip, 1/2" EMT, 1/8"-1/4" Flange.

**CCP1224B:** Conduit to Flange Clip, 3/4" EMT, 1/2" Rigid, 1/8"-1/4" Flange.

**CCP1624B:** Conduit to Flange Clip, 1" EMT, 3/4" Rigid, 1/8"-1/4" Flange.

**CCP1248B:** Conduit to Flange Clip, 3/4" EMT, 1/2" Rigid, 5/16"-1/2" Flange.

**CCP824:** Conduit to Flange Clip, Side Mount, 1/2" EMT, 1/8"-1/4" Flange.

**CCP1224:** Conduit to Flange Clip, Side Mount, 3/4" EMT, 1/8"-1/4" Flange.

**CCP1624:** Conduit to Flange Clip, Side Mount, 1" EMT, 1/8"-1/4" Flange.

**CCP1258:** Conduit to Flange Clip, Side Mount, 3/4" EMT, 5/16"-1/2" Flange.

- EMT sizes from 1/2" to 4"
- Conduit sizes from 1/2" to 4"
- Beam flanges from 1/8" to 1/2" thick
- T-Bar thicknesses – 5/16" and 9/16"
- Rod thickness – 1/4" to 3/8"

---

### SPECIFICATIONS

#### GENERAL INFO

Finish: Black

Quantity: 100

Type: Conduit Clamps

#### TECHNICAL INFORMATION

Material: Spring steel

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA

Buy American Act Status: No