
6FT Q-SERIES CAT6A SNAGLESS SLIM PATCH CORD - WHITE

QCM-A454-02F6-006 | [Quiktron](#)



FEATURES & BENEFITS

Quiktron's Q-Series Cat6a Snagless Unshielded (UTP) Slim 28AWG Network Patch Cords are the perfect solution for high density and top of rack data center applications. The use of 28AWG conductors allows for a 23% reduction in diameter over a standard Cat6a network patch cable. Constructed with high-quality wire and a shortened body plug, these Cat6a patch cords keep Near-end Crosstalk (NEXT) levels to a minimum while providing the necessary bandwidth to support mission-critical applications.

- Factory terminated for superior performance
- Meets or exceeds industry standards for NEXT and return loss
- Also available in a large variety of colors
- Made with 28 AWG, stranded copper (7 X 36), four twisted pairs, aluminum foil shield (100% coverage) over the cable core and includes a 28AWG stranded tinned drain wire along the outer surface
- Lifetime Warranty **Please contact your Quiktron representative for availability**

SPECIFICATIONS

GENERAL INFO

Cable Type: CAT6A

Color: White

Product Series: Q-Series

Type: Q-Series Snagless

Component Type: Cat6A Patch Cord