
P4300 PROFESSIONAL SERIES PLAYER

NV-P4300-NA | [Nuvo](#)



FEATURES & BENEFITS

With a back-lit touch screen for configuration, system status, and the ability to show zone names, the P4300 Professional Series Player (NV-P4300-XX) is the latest generation of Nuvo Players. Providing 110 Watts of power per zone, this single rack-mount unit delivers high fidelity audio to three independent zones. Your music is always in hand with built-in access to streaming services and the ability to play content from networked computers and your iOS and Android devices.

Super efficient Class D amplifiers provide the best quality audio the Player Portfolio has had to date and P4300 has side mounted heat sinks and no fans to allow convenient, single-space rack mounting. Power output remains consistent and can be set to 4, 6 or 8 ohm within the app during setup. All line inputs and line outputs use a combination 3.5mm analog/Toslink connection.

Check out the [Player Portfolio mobile app](#).

Outside North America? Use -EU, -UK or -AU when ordering.



- Built-in access to streaming services- Spotify, iHeartRadio, TuneIn, Napster, Deezer and SiriusXM
- Easily play music from networked computers, and iOS and Android devices.
- Back-lit touch screen supports easy setup with visible system status, zone names, and more
- A single rack-mount unit delivers high fidelity audio to three independent zones
- Efficient Class D amplifiers with 110 watts per zone at 8, 6 or 4 Ohms
- Side mounted heat sinks and no fans for convenient single-space rack mounting
- 3.5mm combination analog/TOSLINK jacks for line inputs and outputs
- Remote network and device management with [Domotz PRO](#)
- Seamless integration into advanced automation systems from Vantage, Crestron, Control4, KNX, and more - visit the [Player Portfolio third party drivers page](#).

*Streaming services subject to geographic availability. Service subscriptions may be required.

SPECIFICATIONS

GENERAL INFO

Color: Black

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (Metric): 258mm

Depth (US): 10.16"

Height (Metric): 54mm

Height (US): 2.13"

Width (Metric): 430mm

Width (US): 16.93"

Overall Dimensions (Metric): 54mm H x 430mm W x 258mm D

Overall Dimensions (US): 2.13" H x 16.93" W x 10.16" D

Primary Packaging Weight (Metric): 3.92kg

Product Weight (Metric): 2.9kg

Product Weight (US): 6.45lbs

TECHNICAL INFORMATION

AC Voltage Input: 110 to 240 VAC @ 50/60 Hz

Connection Method: Ethernet

Frequency Response: 20Hz - 20KHz +/- 1 dB

Humidity: 70% Non-Condensing

LAN Ports: (RJ45, Cat5 minimum, 10/100baseT minimum)

Operating Temperature (Celsius): 0° C to 40° C

Output And Line Out Connection: 3.5mm combination analog/TOSKINK

Output Impedance: 470 Ohms

Power Requirements: 110/240 VAC 50/60Hz

Speaker Impedance Load: 8,6 or 4 Ohms