

---

## P400 PLAYER PORTFOLIO TABLETOP SPEAKER

NV-P400-NA | [Nuvo](#)



---

### FEATURES & BENEFITS

The P400 Tabletop Speaker (NV-P400-XX) easily expands the Player Portfolio system to any room of the home; playing audio in a single zone or staying perfectly in sync when all rooms are singing the same song.

With a powerful 2.1 system, the P400 is an all-in-one stereo speaker and amp. It fills any space with dynamic, rich audio from networked music collections or a near-infinite variety of streaming sources. Controlling the Tabletop Speaker is easy using the Player app on iOS or Android devices, Nuvo in-wall keypads, or the capacitive touch controls on the Tabletop Speaker; convenient for when your phone is out of reach.

Check out the [Player Portfolio mobile app](#).

Outside North America? Use -EU, -UK or -AU when ordering.



- Powerful 2.1 system, complete with a five and a quarter inch subwoofer, two midrange drivers and two tweeters
- Adds a single zone to any Player Portfolio system for easy expansion into any room
- Convenient control options using the Nuvo Player app, optional in-wall keypads, or responsive capacitive touch controls on the device
- Instant access to networked audio content and streaming services – Spotify, Pandora, iHeartRadio, TuneIn, Napster, Deezer, and SiriusXM
- Connects wirelessly or by Ethernet to the home network for seamless integration
- Plug any audio device into the 3.5mm analog audio or USB 2.0 inputs to listen instantly
- Third-party integration with control partners such as Vantage, Crestron, Control4, KNX, RTI, URC, and more - visit the [Player Portfolio third party drivers page](#)
- Remote network and device management with [Domotz PRO](#)

\*Streaming services subject to geographic availability. Service subscriptions may be required.

---

## SPECIFICATIONS

### GENERAL INFO

Color: Black

Input Plug Type: 3.55mm analog/USB 2.0

### DIMENSIONS

Depth (Metric): 149mm

Depth (US): 5.88"

Height (Metric): 368mm

Height (US): 14.5"

Width (Metric): 217mm

Width (US): 8.56"

Overall Dimensions (Metric): 368mm x 217mm x 149mm

Overall Dimensions (US): 14.5" x 8.56" x 5.88"

### TECHNICAL INFORMATION

AC Voltage Input: 100 to 240 VAC @ 50/60 Hz

Frequency Response: 50Hz - 20KHz

Humidity: 70% Non-Condensing

LAN Ports: (RJ45, Cat5 minimum, 10/100baseT minimum)

Operating Temperature (Celsius): 0° C to 32° C

Power Peak: 80W

Power Requirements: 110/240 VAC 50/60Hz