
P5050 PROFESSIONAL SERIES PLAYER

NV-P5050-NA | [Nuvo](#)



FEATURES & BENEFITS

Designed exclusively for integrators, the P5050 Professional Series Player is purpose-built for custom audio installations. Providing 25 watts of power per channel at 8 ohms or 50 watts of power per channel at 4 ohms, the P5050 covers three listening zones in a space and energy efficient 1U rack design. It offers built-in access to endless music options including the most popular streaming music services and networked music collections.

The P5050 can be hard-wired with other Players for centralized integration and system scalability. Offering quick installation, easy setup, convenient control options, and simplified integration with leading automation systems, Nuvo makes it easy to fill any space with uncompromising sound.



- Built-in access to streaming services, including Spotify, Pandora, iHeartRadio, TuneIn, Napster, Deezer, and SiriusXM or personal music collections on networked devices
- Convenient control options including the intuitive Player app, optional in-wall keypad and touch screen, or with Amazon Alexa
- Delivers high-fidelity audio to three independent zones with 25 watts of power per channel at 8 ohms or 50 watts of power per channel at 4 ohms
- Side-mounted heat sinks with no fans support the space and energy efficient 1U rack design
- Compatible with Legrand's other Nuvo Players for a truly custom, flexible home audio solution
- Connect to storage devices, analog equipment or home theater receivers through the units' analog audio line-in, line-out, or USB ports
- Seamless integration into advanced automation systems from Vantage, Crestron, Control4, KNX, and more - visit the [Player Portfolio third party drivers page](#)
- Remote network and device management with [Domotz PRO](#)
- Two-year warranty

SPECIFICATIONS

Line Input: (3) TRS 3.5 mm analog stereo jack

Line Output: (3) TRS 3.5 mm analog stereo jack

Rated Output Power (1KHz/1% Distortion): 4 Ohm 100 W (50 W x 2), 6 Ohm 75 W (37.5 W x 2), 8 Ohm 50 W (25 W x 2)

Total Harmonic Distortion (1/2 Power): 100 Hz 0.005%, 1 KHz 0.005%, 6.67 KHz 0.020%

Damping Factor: 80+

Signal-to-Noise-Ratio, Rated Output: 100 dBa

Output Level: 0-2.0 V RMS

Input Impedance: 10 kOhms

Input Overload: 2.3 V RMS

Power Consumption: 42 W

Music File (USB or over network): MP3 (.mp3), WMA (.wma), AAC (.acc), Ogg Vorbis (.ogg), FLAC (.flac), WAV (.wav)

Streaming Music Services: Amazon Music*, Deezer, iHeart Radio, Napster, Pandora, SiriusXM, Spotify, TuneIn

Playlist Support: WPL, M3u, PLS, iTunes

Safety: cTUVus, CE-LVD

EMC: FCC, IC, CE-EMC, C-Tick

Environmental: RoHS

**when initiated via Amazon Alexa*

DIMENSIONS

Overall Dimensions (Metric): 250mm D x 430mm W x 44mm H

Overall Dimensions (US): 9.84" D x 16.93" W x 1.73" H

Product Weight (Metric): 3.5kg

Product Weight (US): 7.6lbs

TECHNICAL INFORMATION

Frequency Response: (20 - 20kHz) +/-0.5 dB

Operating Temperature (Celsius): 0° C to 40° C

Output Impedance: 470 Ω

Power Peak: 407W

Power Requirements: 100 – 240VAC, 50/60 Hz

Speaker Impedance Load: 4-8Ω