



LYRIQ FLUSH MOUNT SINGLE SOURCE INPUT

AU1004-WH | [On-Q](#)

FEATURES & BENEFITS

Distributes high quality audio to multiple locations throughout the home with the similar functionality as the AU7398, plus additional features.



- Automatically overrides the remote source
- For use with the lyriQ Audio System

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes
Color: White
Product Series: Studio

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Spec 1: Voltage Requirements
Installation Location: In-Wall

CORD INFORMATION

Pinning:
1. Green/White L- (PreGND)
2. Green L+
3. Audio R-

Orange/White(PreGND)
4. Blue IR_IN (IR TX)
5. Blue/White Status_Out (IR RX)
6. Orange Audio R+
7. Ground
Brown/White
8. Brown Power (+24 Vdc)

TECHNICAL INFORMATION

Frequency Response: 20 - 100Hz \pm 4dB; 100 - 20,000Hz \pm 2dB
Humidity: Up to 90% RH (non-condensing)
IR Receive Frequency: 10 KHz \pm 5 KHz to 110 KHz \pm 5 KHz
Power Requirements: +24Vdc supplied by the Distribution Module
Storage Temperature: -25 to +75 Degrees Celsius