



## DIGITAL AUDIO TWO-ROOM, SINGLE-SOURCE KIT, WHITE

AU7152-WH | [On-Q](#)

### FEATURES & BENEFITS

The AU7152-WH is a two-room, single-source Digital Audio Kit. Conveniently supplying all of the core components necessary to install a two-room Digital Audio System with digital source accessibility, this kit comes complete with (2) AU7010-WH Digital Audio Amplified Keypads, (1) AU7000 Digital Audio Distribution Module, (1) AU7001 Digital Audio Input Module, (1) PW1020 Digital Audio Power Distribution Module, (1) PW1060 Power Supply, and (1) PW7760 Power Supply.

Check out the [Digital Audio mobile app](#).



- Comes complete with all core components for a two-room, single-source Digital Audio System with digital source accessibility
- Built-in access to streaming services including, Spotify, iHeartRadio, Pandora, Napster, SiriusXM, and TuneIn
- Allows streaming of networked digital content from iTunes, Windows Media Player libraries, and mobile devices
- Provides 20 watts of Class D power per zone
- Conveniently controllable through both included keypads as well as free, intuitive Android or iOS apps for smartphones and tablets
- Provides all core components needed to install a two-room, single-source Digital Audio System with digital source accessibility
- Structured wiring based to offer easy installation and a repeatable solution
- Simple setup using smartphone or tablet, no PC required
- Available in a four-room kit (AU7254-WH)

\*Streaming services subject to geographic availability. Service subscriptions may be required.

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Connect Cat5e or better and speaker wire 18-16 gauge.  
Color: White  
Size: 8.25" x 8.25" x 13.5"  
Termination: 918.84 cu. in.  
Connection Type: RJ45 connections and removeable pheonix screw down terminals  
Type: Low Voltage, Audio System  
Special Features: 2-Zone, 1-Source Digital Audio System  
Style: Decorator Keypad; Structured wiring cabinet (not included)

#### **LISTING AGENCIES/THIRD PARTY CERTIFICATIONS**

RoHS: Yes  
FCC Standard: Yes  
UL Standard: Yes

#### **DIMENSIONS**

Depth (Metric): 342.9mm  
Depth (US): 13.5"  
Width (Metric): 209.55mm  
Width (US): 8.25"  
Primary Packaging Weight (Metric): 2.31 kg  
Product Weight (Metric): 2.31 kg  
Product Weight (US): 5.1 lbs  
Volume: 918.84 cu. in.  
Weight: 5.1 lbs  
Height: 8.25"

#### **TECHNICAL INFORMATION**

Connection Method: Ethernet network  
Mounting: Wall Mount/Enclosure Mount  
Power Requirements: 24 VDC 60W Power Supply / 12 VDC 18W Power Supply  
Supported Standards: FCC, UL, RoHS  
Watts: 20W 8Ω  
Connection Location: Data Control Interface: Ethernet/Digital Keypad

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA