

---

## HDMI REPEATER

AC2100 | [On-Q](#)



---

### FEATURES & BENEFITS

Supports the connection of two High-Speed HDMI with Ethernet cables.



- Boosts the strength of HDMI signal
- Repeater gets 5v power from HDMI source unit
- Supports all 3D TV transmission standards
- Gold plated contacts for maximum signal transfer

---

### SPECIFICATIONS

#### GENERAL INFO

Termination: 19 Pin to 19 Pin

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Height (US): 0.4"

Length (US): 1.75"

Width (US): 0.85 in

#### CORD INFORMATION

Connector Type End One: Female-Type A (Full Size HDMI)

Connector Type End Two: Female-Type A (Full Size HDMI)

#### TECHNICAL INFORMATION

External Power Input: Powered by in-line 5V HDMI bus (from source)

Humidity: Max 93% non-condensing  
Jack Connectors: Gold plated contacts  
Noise Reduction: Removes digital noise