
18GBPS PREMIUM CERTIFIED HDMI CABLE WITH ETHERNET, 7 METER

AC2AP7-BK |



FEATURES & BENEFITS

The Premium Certified HDMI Cables with Ethernet have undergone rigorous testing to verify that they comply with the HDMI 2.0b specification and can deliver 4K UltraHD, HDR, and other advanced features. Each cable bears the Premium HDMI Certification label to guarantee authenticity.

The Premium Certified Cables feature a smaller overmold for easier pulling between studs or wiring through articulating mounts. The enhanced retention clips on the connector head keep the cable firmly in place and require 4.5lbs of pulling force to remove. This ensures the most secure connection points, maximizing signal integrity and reducing cable-related service calls.

- Premium HDMI Certified to comply with the HDMI 2.0b specification and marked with the anti-counterfeit label to ensure authenticity
- Supports 18.2Gbps bandwidth, UltraHD - 4K@60Hz 4:4:4, High Dynamic Range (HDR), Deep Color, ARC, Ethernet
- Available in lengths 1-7 meters
- Enhanced retention clips keep the cable firmly in place, requiring 4.5lbs of pulling force to remove
- Small overmold for easier pulling between studs or through articulating mounts
- Rated: CMG / CL2-3
- Ideal applications: residential home theater, flat panel installations

SPECIFICATIONS

GENERAL INFO

Cable Type: Type A, 19PIN Male
Color: Black

DIMENSIONS

Length (Metric): 7m
Length (US): 7m
Width (Metric): 7
Width (US): 7

CORD INFORMATION

Connector Type End One: Type A, 19PIN Male

Connector Type End Two: Type A, Male (full sized HDMI),
Cord Length Metric: 7m
Cord Length US: 7m

TECHNICAL INFORMATION

Humidity: 10 ~ 90%, Relative Humidity (non-condensing)
Material: PVC Molding Housin
Operating Temperature (Celsius): 0° ~ 43°C
Output And Line Out Connection: HDMI
Supported Standards: In Wall Rated UL CL-3, RoHS
Wire Gauge: 24 AWG