
10GBPS HIGH-SPEED HDMI CABLES WITH ETHERNET, 0.7 METER

AC2M00-BK | [On-Q](#)



FEATURES & BENEFITS

Not every job requires full 4K support. Some just need a dependable HDMI cable to support 1080p resolution. These 10Gbps High-Speed HDMI Cables with Ethernet are just that. They're tested to deliver uncompressed high-definition audio and video, as well as Ethernet connectivity, at an affordable cost.



- Supports: 100Gbps bandwidth, 1080 resolution, 7.1 digital surround sound, 3D, ARC, Ethernet
- Available in lengths from 1 to 20 meters
- (HEC) capable gold plated connector with individually shielded conductors
- Rated: CMG / CL2-3 / FT4
- Ideal applications: budget home theater, desktop, commercial digital signage, conference room displays

SPECIFICATIONS

GENERAL INFO

Cable Type: CL3 rated for in wall installations

Color: Black

Color Cable Jacket: Black

Termination: 19 Pin to 19 Pin

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CORD INFORMATION

Connector Type End One: Type A (Full Size HDMI)

Connector Type End Two: Type A (Full Size HDMI)

Cord Length Metric: 0.7 m

Cord Length US: 2.3'

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing
Jack Connectors: 24K Gold plated connector
Material: 99.99% Oxygen Free Copper Conductors
Noise Reduction: Triple Shielded
Performance Rating: 4K x 2K resolution supported
Wire Gauge: 30AWG

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA