

---

## IN-WALL TV POWER AND CABLE MANAGEMENT KIT - WHITE

CPT306W-V1 | [On-Q](#)



---

### FEATURES & BENEFITS

Easily hide power and AV cables inside the wall without modifying electrical wiring. This pre-wired kit includes everything needed to extend power to wall mount TV installations while providing the ultimate flexibility with the innovative decorator based power inlet strap and the recessed box with duplex power receptacle.

- Extend power to a wall mount TV without modifying the homes existing electrical wiring
- Tamper Resistant receptacle powers multiple devices such as a TV, sound bar or streaming players
- Recessed receptacle supports almost any type of power plug including right angles and wall warts
- Unique decorator based power inlet strap provides flexible project support for ganging other AV connections
- Hides both power and AV cables inside the wall for a clean, professional installation

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Top: WHITE, Bottom: WHITE

Number Of Ports: 1

Installation Destination: Indoor - Not intended for Fire-Rated walls

#### ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: In-Wall

Mounting Hardware Included: Yes

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

ETL Listing No: Conforms to: UL STDs 514C & 498

ETL Listed: Yes

UL Listing No: UL514C and UL-498

#### DIMENSIONS

Mounting Depth Max: 3.75" (2 x 4 Studed Wall + Drywall)

Overall Dimensions (Metric): 261mm x 104mm x 222mm

Overall Dimensions (US): 10.25" x 4.1" x 8.75"

Product Weight (Metric): .98kg

Product Weight (US): 2.14lbs

## **CORD INFORMATION**

Cord Length US: 6'

## **TECHNICAL INFORMATION**

Amps: 15A

Drywall Hole Size: Top: 5.38"W x 7.13"H, Bottom: 2.25"W x 3.75"H

Material: Plastic

Minimum Depth Requirement (US): 3.75"

Mounting: Wall Mount

NEMA Rating: NEMA 5-15R

Storage Temperature: 32°F to 122°F

Supported Standards: NEMA 5-15R

Volts (AC): 125 VAC

Wire Gauge: 14-2 AWG with Ground - In-Wall Rated

Receptacle Type: 15A Decorator TR

Number Of Outlets: 2