
LYRIQ™ AMPLIFIED KEYPAD, BLACK

AU7394-BK | [On-Q](#)



FEATURES & BENEFITS

Listening to music has never been so easy. The new LyriQ Amplified Keypad allows homeowners to control high quality sound throughout the home and garden. It also offers energy-conscious green features, such as a class D amplifier and a convenient sleep mode.

- Adjustable backlight levels for increasing or decreasing illumination
- Stylish, decorator-style keypad – perfect for any decor
- Provides 50% in energy savings
- Amplifiers go into standby mode after 20 minutes of non-use
- Improved efficiency due to class D amplification
- Infrared sensors allow easy remote control of volume level and whole house commands

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes

Color: Black

DIMENSIONS

Overall Dimensions (Metric): 105.2x42x61.8mm

Overall Dimensions (US): 4.14"H x 1.65"W x 2.43"D

Weight: 0.260 lb (118g)

CORD INFORMATION

Pinning:

1. Green/White L- (PreGND)
2. Green L+
3. Orange/White Audio R- (PreGND)
4. Blue IR_IN (IR TX)
5. Blue/White Status_Out (IR RX)

- 6. Orange Audio R+
- 7. Brown/White Ground
- 8. Brown Power (+24 Vdc)

TECHNICAL INFORMATION

External Power Input: +24-30Vdc

Frequency Response: 20-20,000Hz \pm 2dB

IR Range On Axis: 25ft Max; IR Range 30 degrees off-axis 20ft max

IR Receive Frequency: 10KHz - 110KHz

Material: ABS Plastic/Aluminum

Mounting: Dimensions: 4.14"H x 1.65"W x 2.05"D (105.2x42x52.1mm)

Output And Line Out Connection: 14-28 AWG Springcon® Terminal Block AWG Springcon® Terminal Block

Output Impedance: 8 Ω (1 pair of speakers)

Power Requirements: +24Vdc \pm 6Vdc, 500mA average

BUY AMERICAN ACT COMPLIANCE

Buy American Act Status: Exception

Note: Contact Customer Support for Buy American Act options