

---

## LYRIQ AMPLIFIED VOLUME CONTROL WITH IR, LIGHT ALMOND

F7399-LA | [On-Q](#)



---

### FEATURES & BENEFITS

Listening to music has never been easier or this much fun. Our new Cat 5 based audio system features multi-zone distribution and new, stylish keypad volume controls. The On-Q lyriQ Audio System can deliver high quality sound throughout the home and garden and lets your homeowners control it all to suit their mood.

#### DISCONTINUED

- Infrared sensors allow easy remote control of volume level and whole house commands
- Stylish, decorator-style volume control - perfect for any decor

---

### SPECIFICATIONS

#### GENERAL INFO

Discontinued: Yes

Color: Light Almond

#### DIMENSIONS

Overall Dimensions (Metric): 105.2x42x61.8mm

Overall Dimensions (US): 4.14"H x 1.65"W x 2.43"D

Weight: 0.260 lb (118g)

#### CORD INFORMATION

Pinning:

1. Green/White L- (PreGND)
2. Green L+
3. Orange/White (PreGND) Audio R-
4. Blue IR\_IN (IR TX)
5. Blue/White Status\_Out (IR RX)
6. Orange Audio R+
7. Brown/White Ground

8. Brown Power (+24  
Vdc)

#### TECHNICAL INFORMATION

External Power Input: +24-31Vdc

Frequency Response: 20-20,000Hz  $\pm$  2dB

IR Range On Axis: 15-55 ft

IR Receive Frequency: 10KHz - 110KHz

Material: ABS Plastic/Aluminum

Mounting: Dimensions: 4.14"H x 1.65"W x 2.05"D (105.2x42x52.1mm)

Output And Line Out Connection: 14-28 AWG Springcon® Terminal Block AWG Springcon® Terminal Block

Output Impedance: 8  $\Omega$  per channel (1 pair of speakers)

Power Requirements: +24Vdc  $\pm$  6Vdc, 500mA max