
UNITY RS232 LIGHTING INTERFACE

LC2354 | [On-Q](#)

FEATURES & BENEFITS

The LC2354 allows the Unity Home System to communicate with the RF Lighting Control system. This simple kit combines the RF Lighting Control Serial Interface with a Unity Interface Adaptor (DB9 to RJ45) and connects to Serial Port1 on the Unity Integration Module. Includes a 12V DC power supply and must be mounted within 20 feet of the Unity Integration Module.

The kit includes:

- RF Lighting Control Serial Interface with a Unity Interface Adapter.
- 12V DC power supply.

The LC2354 must be mounted within 20 feet of the Unity Integration Module

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 5
Color: Black
Connection Type: DB9 to RJ45 Adaptor
Type: Unity to RF Lighting Interface

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

FCC Standard: Yes
UN SPSC: 39121107

CONSTRUCTION INFORMATION

Installation Location: Central location in system

DIMENSIONS

Depth (Metric): 2.5 cm
Depth (US): 1"
Length (Metric): 9.4 cm
Length (US): 3.69 in
Width (Metric): 9.5 cm
Width (US): 3.75 in

CORD INFORMATION

Connector Type End One: DB9
Connector Type End Two: RJ45

TECHNICAL INFORMATION

Compatible Power Supplies: AC Adapter provided accepts 120VAC at 60 Hz and provides 9VDC 50mA
Frequency: 900MHz, Patented Top Dog™ Frequency-agile RF Wireless
Operating Temperature (Celsius): 0°C to 40°C
Supported Standards: FCC PART 15 B