
INTERCOM PATIO UNIT, OUTDOOR, WHITE

F7641-WH | [On-Q](#)



FEATURES & BENEFITS

The Broadcast Intercom Patio Unit includes most of the options available in an indoor room unit, but in a weatherproof version. It can be turned off from the main console for security reasons, and is available in classic finishes to enhance the curb appeal of any home.

- **Stylish metal design complements outdoor living areas.**
- **Installs in standard double gang opening.**
- **Can be disabled from the main console.**
- **Weatherproof finish.**
- **Multi-level volume control.**
- **Page, monitor, and do not disturb features.**

SPECIFICATIONS

GENERAL INFO

Cable Type: Cat 5e
Color: White
Connection Type: 110 IDC Punchdown
Type: Intercom Unit

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

FCC Standard: Yes
UN SPSC: 43221525

DIMENSIONS

Depth (Metric): 3.2 cm
Depth (US): 1.25"
Height (Metric): 12 cm
Height (US): 4.71"
Width (Metric): 12.1 cm
Width (US): 4.77 in

CORD INFORMATION

Pinning:

- | | |
|-----------------|-------------------------|
| 1. Green/White | Audio Direction Control |
| 2. Green | Monitor Button |
| 3. Orange/White | Power (12V) |
| 4. Blue | Ground |
| 5. Blue/White | Audio In |
| 6. Orange | Audio Out |
| 7. Brown/White | Talk Button |
| 8. Brown | Door Button |

TECHNICAL INFORMATION

External Power Input: Power over Ethernet via Intercom Module

Frequency: Speaker: 100-20000 Hz

Frequency Response: Microphone: 20 - 16000 Hz

Humidity: 90% Relative Humidity (Non-Condensing)

Mounting: Double-Gang Electrical Box

Operating Temperature (Celsius): -25°C to 55°C

Power Peak: Speaker: 5 Watts

Power RMS: Speaker: 3 Watts