



IN-WALL FORWARD-PHASE UNIVERSAL DIMMER, IVORY

DRD4-I | [On-Q](#)

FEATURES & BENEFITS

The DRD4 in-wall forward-phase dimmer operates most dimmable lighting types including incandescent, dimmable fluorescent, dimmable LED, dimmable cathode, and neon. As part of the RF Lighting Control System, it can be controlled from other devices located anywhere in the home.

- Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.
- Patented overload and short circuit protection.
- No control wiring necessary.
- Large surface-mounted antenna ensures maximum broadcast coverage.
- Stores room and house scenes.
- Compatible with Decorator wall plates.
- 5-year warranty.
- **Note:** Wall plate sold separately from device.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Connection Type: Screw Terminals
Type: RF Dimmer

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005
CSA Standard: Yes
cUL Standard: Yes
FCC Standard: Yes
UL Listing No: UL 244A
UL Standard: Yes
UN SPSC: 39122206

DIMENSIONS

Depth (Metric): 4.8 cm

Depth (US): 1.88"
Height (Metric): 10.8 cm
Height (US): 4.25"
Width (Metric): 4.3 cm
Width (US): 1.69"

TECHNICAL INFORMATION

Frequency: 900 MHz
Humidity: 0-80% relative humidity, noncondensing
Material: High Impact Plastic
Mounting: Electrical Box
Operating Temperature (Celsius): 0°C to 40°C
Reset: Press and hold up and down buttons
Supported Standards: Topdog™ RF communication protocol
Volts (AC): 120 VAC
Watts: 25W - 600W loads supported