



IN-WALL 3-WAY SWITCH, ALMOND

DRD8-A V2 | [On-Q](#)

FEATURES & BENEFITS

As part of the RF Lighting Control System, the DRD8 in-wall 3-way switch provides convenient control from multiple access points when used in conjunction with any wireless switch or dimmer.

- Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.
- Patented overload and short circuit protection.
- No control wiring necessary.
- Large surface-mounted antenna ensures maximum broadcast coverage.
- Stores room and house scenes.
- Compatible with Decorator wall plates.
- 5-year warranty.
- **Note:** Wall plate sold separately from device.

SPECIFICATIONS

GENERAL INFO

Discontinued: Yes

Color: Almond

Connection Type: Screw Terminals

Type: Multiple Dimmer/Switch Controller

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005

CSA Standard: Yes

cUL Standard: Yes

FCC Standard: Yes

UL Listing No: UL 244A

UL Standard: Yes

UN SPSC: 39121107

DIMENSIONS

Depth (Metric): 4.8 cm

Depth (US): 1.88"

Height (Metric): 10.8 cm
Height (US): 4.25"
Width (Metric): 4.3 cm
Width (US): 1.69"

TECHNICAL INFORMATION

Frequency: 900 MHz
Humidity: 0-80% relative humidity, noncondensing
Material: High Impact Plastic
Mounting: Electrical Box
Operating Temperature (Celsius): 0°C to 40°C
Reset: Press and hold up and down buttons
Supported Standards: Topdog™ RF communication protocol
Volts (AC): 120/277 VAC