



## IN-WALL WHOLE HOUSE SCENE CONTROLLER, BLACK

DRD5-B V2 | [On-Q](#)

### FEATURES & BENEFITS

As part of the RF Lighting Control System, the DRD5 in-wall whole house scene controller allows for effortless lighting control for the entire home from any location. Easy one-button scene recall allows users to turn lights on and off with the press of a button. Perfect for entrance and exit points of the home.

- **Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.**
- **Patented overload and short circuit protection.**
- Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.
- Patented overload and short circuit protection.
- No control wiring necessary.
- Large surface-mounted antenna ensures maximum broadcast coverage.
- Stores room and house scenes.
- Compatible with Decorator wall plates.
- 5-year warranty.
- **Note:** Wall plate sold separately from device.

### SPECIFICATIONS

#### GENERAL INFO

Discontinued: Yes

Color: Black

Connection Type: Screw Terminals

Type: House Scene Interface

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005

CSA Standard: Yes

cUL Standard: Yes

FCC Standard: Yes

UL Listing No: UL 244A

UL Standard: Yes

UN SPSC: 39121107

## DIMENSIONS

Depth (Metric): 4.8 cm

Depth (US): 1.88"

Height (Metric): 10.8 cm

Height (US): 4.25"

Width (Metric): 4.3 cm

Width (US): 1.69"

## TECHNICAL INFORMATION

Frequency: 900 MHz

Humidity: 0-80% relative humidity, noncondensing

Material: High Impact Plastic

Mounting: Electrical Box

Operating Temperature (Celsius): 0°C to 40°C

Reset: Press and hold up and down buttons

Supported Standards: Topdog™ RF communication protocol

Volts (AC): 120/277 VAC