



## IN-WALL FAN SPEED CONTROLLER, BLACK

DRD9-B | [On-Q](#)

### FEATURES & BENEFITS

This controller gives you four options for ceiling fan speed and includes a built-in de-hummer to reduce fan noise.

- **Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.**
- **Patented overload and short circuit protection.**
- Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.
- Patented overload and short circuit protection.
- No control wiring necessary.
- Large surface-mounted antenna ensures maximum broadcast coverage.
- Stores room and house scenes.
- Compatible with Decorator wall plates.
- 5-year warranty.
- **Note:** Wall plate sold separately from device.

### SPECIFICATIONS

#### GENERAL INFO

Color: Black

Connection Type: Screw Terminals

Type: RF Fan Control

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: 22.2 No. 156-M1987

CSA Standard: Yes

cUL Standard: Yes

FCC Standard: Yes

UL Listing No: ANSI/UL 1917

UL Standard: Yes

UN SPSC: 39122215

#### DIMENSIONS

Depth (Metric): 4.8 cm

Depth (US): 1.88"  
Height (Metric): 10.8 cm  
Height (US): 4.25"  
Width (Metric): 4.3 cm  
Width (US): 1.69"

#### TECHNICAL INFORMATION

Amps: 1.5A  
Frequency: 900 MHz  
Humidity: 0-80% relative humidity, noncondensing  
Material: High Impact Plastic  
Mounting: Electrical Box  
Operating Temperature (Celsius): 0°C to 40°C  
Reset: Press and hold up and down buttons  
Supported Standards: Topdog™ RF communication protocol  
Volts (AC): 120 VAC