

---

## CAT 6 48-PORT RACK MOUNT PATCH PANEL

48845CC6 | [On-Q](#)



---

### FEATURES & BENEFITS

This 48 port universal 568A/B Category 6 rack mount patch panel takes up a single rack space (1U). The patch panel performance exceeds the TIA Category 6 Patch Panel Standards. It supports data rates up to 10 Gigabits. It offers many cable management features such as rear cable management bar, cable ties for strain relief, and front facing labels.



- Supports 48 network connections up to 10 Gigabit Ethernet speeds.
- Included Cable Management bar secures rear cables and provide strain relief.
- Exceeds the TIA/EIA-568 standard for connecting hardware.

---

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Cat 6  
Color: Black  
Mod Jack Wiring: T568A/B Universal Wiring  
Type: Rackmount Patch Panel  
Input Plug Type: RJ45 Male

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
cULus: Yes  
FCC Standard: Yes  
UN SPSC: 43223309

#### DIMENSIONS

Depth (Metric): 8 cm

Depth (US): 3"  
Height (Metric): 8.89 cm  
Height (US): 3.5"  
Width (Metric): 48 cm  
Width (US): 19 in

#### **TECHNICAL INFORMATION**

Material: Plastic and Steel  
Mounting: Rack  
Performance Rating: High-performance panel  
Product Fits Into: 19-inch rack  
Receptacle Type: RJ45 Female, 8P8C  
Number Of Receptacles: 48

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN  
Buy American Act Status: No