



## 6-PORT CAT 6 DATA BOARD (FOR MDU ENCLOSURE)

AC0606 |

### FEATURES & BENEFITS

This patch panel provides a termination point for up to six Ethernet drops. It is designed to be specified into an EN0800 enclosure for basic structured wiring applications, such as multi-dwelling units and small homes.



- Package includes one 6-way Cat 6 patch panel
- Also available in Cat5e with the AC0506

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Full Duplex Gigabit Ethernet Cat 6 or better

Color: Green/Black

Finish: Smooth

Number Of Ports: 6

Connection Type: RJ45/IDC

Type: Low Voltage, Data Network Component

Special Features: Punchdown style termination, 6-Port, RJ45 Data Ports

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Depth (US): 0.75"

Height (Metric): 44.5 mm

Height (US): 1.75"

Length (Metric): 19 mm

Width (Metric): 146 mm

Width (US): 5.75"

Rack Units: Custom MDU enclosure mountable

#### **TECHNICAL INFORMATION**

Humidity: 10% - 90% Relative Humidity (non-condensing)

Jack Connectors: Cat 6 RJ45

Material: Plastic

Mounting: Custom MDU enclosure mountable

Operating Temperature (Celsius): -20° C to 75° C

Power Requirements: None

Supported Standards: ANSI/TIA/EIA-568-A

Equipment Type: Full Duplex Ethernet