



12" ENCLOSURE WITH SCREW-ON COVER

EN1200 | [On-Q](#)

FEATURES & BENEFITS

This 12-inch enclosure is the perfect solution for a basic or entry-level structured wiring system. It features large top openings that make pulling wire easier than ever before. The enclosure also boasts multiple knockouts, side lances, and side tabs for more flexible mounting. Includes a screw-on cover.



- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Literature pouch included for dealer information
- Includes self-adhesive cable identification table
- Cover included
- Made in the USA

SPECIFICATIONS

GENERAL INFO

Color: Glossy White
Finish: Protective Powder Coat
Type: Screw-On

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
UL Listing No: ANSI/UL 1863; CAN/CSA-C22.2 No. 182.4-1990 -- (Communication Circuit Accessory)

DIMENSIONS

Depth (US): 3.7"

Height (US): 12.13"

Width (US): 14.3"

Product Weight (US): 6.5 lb

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing

Material: 20 Gauge CRS

Minimum Depth Requirement (US): 3.7"

Mounting: Surface or Flush