
14" ENCLOSURE WITH SCREW-ON COVER

EN1400 | [On-Q](#)

FEATURES & BENEFITS

This 14" On-Q enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a screw-on cover.



PRODUCT
ENVIRONMENTAL PROFILE

- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Cover included
- Made in the USA

SPECIFICATIONS

GENERAL INFO

Color: Glossy White
Finish: Protective Powder Coat
Type: Screw-On

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
UL Listing No: ANSI/UL 1863;ANSI/UL 985;ANSI/UL 1023; CAN/CSA-C22.2 No. 182.4-1990;ULC-S545;CSA-C22.2 No. 144.1 (2006) -- (Communication Circuit Accessory) and (Security Equipment - Fire Alarm Equipment)

DIMENSIONS

Depth (US): 3.7"
Height (US): 14.1"
Width (US): 14.3"
Product Weight (US): 8.46 lb

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing
Material: 20 Gauge CRS
Minimum Depth Requirement (US): 3.7"
Mounting: Surface or Flush