



28" ENCLOSURE WITH HINGED DOOR

EN2850 | [On-Q](#)

FEATURES & BENEFITS

This 28" enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes a hinged cover.



- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Literature pouch included for dealer information
- Includes self-adhesive cable identification table
- Cover included
- Made in the USA

SPECIFICATIONS

GENERAL INFO

Color: Glossy White
Finish: Protective Powder Coat
Type: Hinged

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
UL Listing No: ANSI/UL 1863;ANSI/UL 985;ANSI/UL 1023; CAN/CSA-C22.2 No. 182.4-1990;ULC-S545;CSA-C22.2 No. 144.1 (2006) -- (Communication Circuit Accessory) and (Security Equipment - Fire Alarm Equipment)

DIMENSIONS

Depth (US): 3.7"

Height (US): 28"

Width (US): 14.3"

Product Weight (US): 15.0 lb

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing

Material: 20 Gauge CRS

Minimum Depth Requirement (US): 3.7"

Mounting: Surface or Flush